

Project Name

Location

Prepared By



## NUVO 65-752

LED SMALL 20W ROUND WALL PACK

**Notes**

[www] 01-25-2021 01:02:05

**General**

Status	Active
Fixture Type	Area Light
Finish	White
Wattage	20
Lumen Output	2600L - 2800L
CCT (Kelvin)	3000K/4000K/5000K
IP Rating	IP65
Indoor or Outdoor Fixture	Outdoor

**Specifications**

Technology	LED
CRI	80
Voltage	120V-277V
Beam Angle	100
Rated Hours	50000
Operating Temperature	-30C (-22F) to a maximum of +45C (+113F)
Dimmable	Yes - Dimmable
Photocell	Yes - Bypassable
Surge Protection	Built-in surge protection - 2.5KV
Weight (lb.)	2.42
Material	Die-cast Aluminum

**Dimensions**

Height (in.)	8.70
Extension (in.)	3.40

**Compliance**

Safety Listing	cULus
Location Rating	Wet
DLC Approved	Yes
DLC ID	PLGEPXY78U37
California Status	California T24 Compliant
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

**Additional Information**

Additional Information	UV stabilized powder coated finish
Warranty	5 Year Limited - Fixtures