

Project Name

Location

Prepared By



Notes

[www] 01-25-2021 01:02:07

**General**

Status	Active
Watts	6.5
Incandescent Equivalent	50
Fluorescent Equivalent	11.00
Volts	120V
Shape	PAR20
Base	Medium
ANSI Base	E26
Finish	Silver
CCT (Kelvin)	4000
Temperature	Cool White
CRI	90
Lumens	520
Beam Spread	40
Dimmable	Yes - Dimmable
Hours Rated	25000
Lamp Type	PAR
Technology	LED

**Electrical**

Operating Frequency	60 Hz
CBCP	593
Dimming Type	Thyristor
Power Factor	0.9
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

**Physical**

MOL	2.99
MOD	2.44
Lensed	Lensed Lamp
Lens Finish	Clear
Lens Material	Thermo Plastic
Housing Color	Silver
Weight (lb.)	0.10

**Additional Information**

Rated For Enclosed Fixture	Yes
Warranty	3 Year Limited - 12 hr per day

**Compliance**

Safety Listing	cULus
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2366412
California Status	California T24 Compliant
Nevada Status	Lawful for sale in Nevada
RoHS Compliant	Yes
FCC Compliant	Yes

