

Project Name

Location

Prepared By



SATCO S9430

13PAR30/LN/LED/40/2700K/120V

Notes

[www] 01-25-2021 01:02:03

General

Status	Discontinued
Substitute	S29430
Watts	13
Incandescent Equivalent	75
Volts	120V
Shape	PAR30LN
Base	Medium
ANSI Base	E26
Finish	Clear
CCT (Kelvin)	2700
Temperature	Warm White
CRI	82
Lumens	1000
Beam Spread	40
Dimmable	Yes - Dimmable
Hours Rated	25000
Lamp Type	PAR
Technology	LED

Electrical

CBCP	1300
Power Factor	1
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	4.59
MOD	3.75
Lensed	Lensed Lamp
Housing Color	Silver

Additional Information

Rated For Enclosed Fixture	Yes
IP Rating	IP65
Warranty	3 Year Limited - 12 hr per day

Compliance

Safety Listing	cULus
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2292763
California Status	Non-Compliant
California Compliant Substitute	S9487
RoHS Compliant	Yes
SDS Sheet	LED_Lamp