SATCO' NUVO

Project Name

Location

Prepared By



NUVO 65-583

1X4 LED BACKLIT FLAT PANEL

Notes

General Status Active Finish White 40 Wattage Lumen Output 4200L - 4400L 3500K/4000K/5000K CCT (Kelvin) IP20 **IP** Rating Indoor or Outdoor Fixture Indoor Specifications Technology LED CRI 80+ 100V-347V Voltage Beam Angle 120 Rated Hours 50000 -17C (+1.4F) to a maximum of +45C **Operating Temperature** (+113F) Dimmable 0-10V Dimming Only Photocell No Photocell Lens Material PMMA Weight (lb.) 4.98 Material Aluminum and Steel Dimensions Height (in.) 1.50 Width (in.) 11.84 Length (in.) 47.72 Compliance Safety Listing cETLus Location Rating Damp **RoHS** Compliant Yes FCC Compliant Yes Additional Information

Warranty

5 Year Limited - Fixtures

For More Information Visit: <u>https://www.satco.com/</u>

