

Project Name

Location

Prepared By



Notes

[www] 11-09-2020 01:10:25

General

Status	Discontinued
Substitute	S29448
Watts	15
Incandescent Equivalent	90
Volts	120V
Shape	PAR38
Base	Medium
ANSI Base	E26
Finish	Clear
CCT (Kelvin)	4000
Temperature	Cool White
CRI	83
Lumens	1200
Beam Spread	40
Dimmable	Yes - Dimmable
Hours Rated	25000
Lamp Type	PAR
Technology	LED

Electrical

CBCP	1700
Power Factor	1
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	5.19
MOD	4.75
Lensed	Lensed Lamp
Housing Color	Silver

Additional Information

Rated For Enclosed Fixture	Yes
IP Rating	IP65
Warranty	3 Year Limited - 12 hr per day

Compliance

Safety Listing	cULus
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2289546
CEC Status	Non-Compliant
CEC Compliant Substitute	S8497
RoHS Compliant	Yes
SDS Sheet	LED_Lamp