

Project Name

Location

Prepared By



**Notes**

[www] 11-09-2020 01:16:25

**General**

Status	Discontinued
Substitute	S29405
Watts	7
Incandescent Equivalent	50
Volts	120V
Shape	PAR20
Base	Medium
ANSI Base	E26
Finish	Clear
CCT (Kelvin)	2700
Temperature	Warm White
CRI	82
Lumens	525
Beam Spread	40
Dimmable	Yes - Dimmable
Hours Rated	25000
Lamp Type	PAR
Technology	LED

**Electrical**

CBCP	600
Power Factor	0.9
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

**Physical**

MOL	3.03
MOD	2.5
Lensed	Lensed Lamp
Housing Color	Silver

**Additional Information**

Rated For Enclosed Fixture	Yes
IP Rating	IP65
Warranty	3 Year Limited - 12 hr per day

**Compliance**

Safety Listing	cULus
Location Rating	Wet
Energy Star	Yes
ES Unique ID	ESID-2289788
CEC Status	Non-Compliant
CEC Compliant Substitute	S9485
RoHS Compliant	Yes
SDS Sheet	LED_Lamp