

Project Name

Location

Prepared By



NUVO 65-265

LED SMALL WALL PACK W/PHOTOCEL

Notes

[www] 03-09-2021 01:43:24

General

Status	Active
Fixture Type	Wall Pack
Finish	Black
Wattage	20
Lumen Output	2669
CCT (Kelvin)	4000
Temperature	Cool White
IP Rating	IP65
Indoor or Outdoor Fixture	Outdoor

Specifications

Technology	LED
CRI	80+
Voltage	100V-277V
Beam Angle	100
Rated Hours	50000
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)
Dimmable	Non-Dimmable
Photocell	Has Photocell
Lens Material	Polycarbonate (PC)
Weight (lb.)	1.98
Material	Cast Aluminum

Dimensions

Height (in.)	8.59
Width (in.)	5.81
Extension (in.)	3.09

Compliance

Safety Listing	cETLus
Location Rating	Wet
UL Application	Wall
Energy Star	No
DLC Approved	Yes
DLC ID	PL4CSAID118R
ADA Compliant	Yes
California Status	California T24 Compliant
California Prop 65	Lead
RoHS Compliant	Yes

Additional Information

Warranty	5 Year Limited - Fixtures
----------	---------------------------