

Project Name

Location

Prepared By



SATCO S9918

43T8/LED/96-840/BP 120-277V

Notes

[www] 03-01-2021 00:54:16

General

Status	Active
Watts	43
Fluorescent Equivalent	54W/59W
Volts	120V-277V
Ballast Type	Type B
Shape	T8
Base	Single Pin
ANSI Base	Fa8
Nominal Length	96
Finish	Gloss White
CCT (Kelvin)	4000
Temperature	Cool White
CRI	82
Lumens	5500
Beam Spread	210
Dimmable	Non-Dimmable
Hours Rated	50000
Lamp Type	Linear
Technology	LED

Electrical

Ballasting Requirements	Ballast Bypass
Operating Frequency	50/60 Hz
Power Factor	0.9
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	96
MOD	1

Additional Information

Shatter-Proof Type	Yes
Warranty	5 Year Limited - T8 LED Bulbs - Ballast Bypass

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	No
DLC Approved	Yes
DLC ID	PLQLREDLYD4V
California Status	Lawful for sale in California
Nevada Status	Lawful for sale in Nevada
RoHS Compliant	Yes
NSF Approved	Yes - Approved

