

# ESX1 LED

Area Luminaire

## The Best Product, at the Best Price with the Best Delivery

When your project calls for low initial cost and high energy savings, the Lithonia Lighting® ESX1 LED area luminaire delivers. Eight in-stock versions of the ESX1 provide the best combination of lumens, optics, color temperatures, voltages and mounting configurations for replacing 150W to 400W HID luminaires in a wide variety of applications.

All ESX1 luminaires feature adjustable light output, providing two light levels from each luminaire, allowing greater flexibility in the field and on distributors' shelves. A reversible arm facilitates mounting to both round and square poles. Since all eight ESX1 configurations are always in stock at the Acuity Brands regional distribution centers, your project will always be on schedule.



### Quick Facts:

- Replaces 150W to 400W HID
- 8,000 to 25,000 lumens
- Adjustable Light Output (ALO) technology
- Type 3 and Type 5 optics
- 4000K and 5000K CCT
- MVOLT and HVOLT
- Reversible arm mounts onto round and square poles
- DLC Premium listed



# ESX1 LED Area Luminaire

## Benefits for Distributors & Contractors:

The ESX1 offers a complete area lighting package providing everything required to replace 150W to 400W HID luminaires. Adjustable light output provides two light levels from one product, allowing greater flexibility while helping reduce inventory costs. The Lithonia Lighting® ESX1 LED is competitively priced and always in stock for quick delivery.

**Dark Bronze Finish:**  
The most popular color

**Type 3 & 5 Optics:**  
The most popular optics for small and medium-sized parking lots

**Round and Square Pole Mounting:**  
A single reversible arm fits both round and square poles

**Adjustable Light Output (ALO) technology:**  
Internal bi-level switch with two light levels for greater flexibility within one product

	High Lumens	Low Lumens	HID Replacement
ESX1 LED P2	14,000	8,000	150W to 250W
ESX1 LED P4	25,000	21,000	400W

### Best Product

>70% energy savings with superior illumination when replacing HID

### Best Price

Low initial cost ensures quick payback and long-term financial reward

### Best Delivery

All ESX configurations are in stock at Acuity regional distribution centers

HID Equivalent	Series / Power Package	High		Low		Distribution	Voltage	Nomenclature	CI Code	UPC
		Lumens	Watts	Lumens	Watts					
<b>4000K</b>										
150W to 250W	ESX1 LED P2	14,000	98W	8,000	50W	Type 3	120V - 277V	ESX1 LED P2 40K R3 MVOLT UPA BLS DDBXD M2	*269PG3	00194994838302
400W	ESX1 LED P4	25,000	190W	21,000	146W	Type 3	120V - 277V	ESX1 LED P4 40K R3 MVOLT UPA BLS DDBXD M2	*269PG8	00194994838340
							347V - 480V	ESX1 LED P4 40K R3 HVOLT UPA BLS DDBXD M2	*269PGC	00194994838364
						Type 5	120V - 277V	ESX1 LED P4 40K R5 MVOLT UPA BLS DDBXD M2	*269PGG	00194994838418
							347V - 480V	ESX1 LED P4 40K R5 HVOLT UPA BLS DDBXD M2	*269PGN	00194994838463
<b>5000K</b>										
150W to 250W	ESX1 LED P2	14,000	98W	8,000	50W	Type 3	120V - 277V	ESX1 LED P2 50K R3 MVOLT UPA BLS DDBXD M2	*269PGY	00194994838555
400W	ESX1 LED P4	25,000	190W	21,000	146W	Type 3	120V - 277V	ESX1 LED P4 50K R3 MVOLT UPA BLS DDBXD M2	*269PH1	00194994838531
						Type 5	120V - 277V	ESX1 LED P4 50K R5 MVOLT UPA BLS DDBXD M2	*269PH2	00194994838548

Note: Luminaire ships set on high (switchable to low). All luminaires feature adjustable light output, reversible arm mount for round and square poles and dark bronze finish. Wall bracket accessory sold separately and stocked at Acuity Brands distribution centers. The lumen output and input watts are nominal values. Refer to ESX1 specification sheet for specific configuration values.



Please check the DLC Qualified Products List at [www.designlights.org/QPL](http://www.designlights.org/QPL) for more product detail.

Visit [www.lithonia.com](http://www.lithonia.com) for more information