
Philips Halogen Linear

150W RSC base

Clear Dimmable



Brilliant alternative to incandescents

Make work spaces brighter with white light

Philips 150W dimmable halogen linear light bulb provides bright light for work and security tasks. An efficient alternative to 150W incandescents, it has no mercury and saves a lot of money.

Natural light

• Bright alternative to incandescent

- Easy to use
- Dimmable***
- Instant On



Specifications

Bulb characteristics

- Shape: Linear
- Lamp shape code: T3
- Base: RSC
- Voltage: 110-120 VDimmable
- Diminable
- **Power consumption**
- Wattage: 150 W

Light characteristics

Application: Extra brightness

- Color rendering index (CRI): 100
- Color temperature: 2730 K
- Light output: 2400 lumen
- Light effect/finish: Clear

Durability

Average life (at 2.7 hrs/day): 3 year(s)
Lifetime of lamps: 3000 hour(s)

Bulb dimensions

- Height: 3.11 inch
- Width: 0.38 inch

046677116125

Highlights

Dimmable***

This lamp can be used with most dimmers to create your desired ambience with smooth dimming to 10% of full light levels.

Alternative to incandescent

This EcoVantage halogen light bulb provides beautiful light similar to natural daylight, ideal for enhancing your home.

Instant On

Just by turning the switch, your room is at full brightness. No slow starting or waiting.



* **2.7 years means rated average life based on engineering testing and probability analysis where the lamp is used on average 3 hours/day, 7 days a week.