

Actual

Catalog Number: 1000HPS

 Product ID:
 7TAH006110R0000

 UPC Number:
 78378620052

Status: Active

Type HPS - Split-Bolt Connector with Spacer, Conductor Range for Equal Main and Tap AC-SR 900-477, Conductor Range for Equal Main and Tap 1000 kcmil-500 kcmil, Min Tap with One Max Main 4/0 Str, Tin Plated

- Bolt and pressure bar of copper alloy, completely tin plated for corrosion resistance.
   Contoured spacer of bronze alloy copper.
- Splicing, tapping or terminating conductors in power and grounding electrical connection

North American Specifications (UNSPSC)	
UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Туре	Split-Bolt
Special Features	Bolt and pressure bar of copper alloy, completely tin plated for corrosion resistance. Contoured spacer of bronze alloy copper.
Application	Splicing, tapping or terminating conductors in power and grounding electrical connection.
Standard	UL E9809
Material	Copper Alloy
Finish	Electro Tin-Plated
Color	Metallic

European Specifications (ETIM)		
ETIM	EC000491 Earth terminal clamp	
Suitable for	Round conductor	
Material	Copper	
Packaging		
Inner Quantity	1	
Inner Dimensions (inches)	4.09x3.03x2.72	
Outer Quantity	18	
Outer Dimensions (inches)	11x9.8x8	
Weight Uom	2.9 lbs. Each	

Documents / Support Tools			
Technical Drawing / Data Sheet	WSD-000072		
Technical Drawing / Data Sheet Canada	Available on Website		

## For further technical assistance, please contact us...

ABB Installation Products Technical Support

MS 3B-50

860 Ridge Lake Blvd. Memphis, TN 38120 Hours: 7AM - 6PM CDT Monday-Friday Phone: (888) 862-3289 Fax: (901) 252-1321 Email:techsupport@tnb.com

ABB Installation Products - USA 860 Ridge Lake Blvd. Memphis, TN 38120 www.tnb.com