

Stainless Steel Cable Ties and Accessories

Tools and Accessories

Boiler rooms, shipyards, or off-shore oil platforms — a match for any severe environment!

- Stainless steel strap cable ties have been designed for high-temperature applications and for use in areas of harsh, corrosive environments
- Rated at 200-lb. tensile strength
- Smooth edges protect both the cable insulation and the installer



Cat. No.	Body Width (in.)	Length (in.)	Max. Wire Bundle Dia. (in.)	Tensile Strength (lb.)	Std. Pkg.
Ty-Rap® Stainless Steel Strap Cable Ties					
TYS8	0.310	10.65	2	200	100
TYS14	0.310	14.65	4	200	50
TYS22	0.310	22.65	6	200	50
TYS28	0.310	28.65	8	200	50

Note: Use WT3S Tool for tensioning
 Cannot be coated with any covering material
 Made of 316 stainless steel

1,000-ft. reel to cut your desired length!



Cat. No.	Description	Width (in./mm)	Tensile Strength (lb./N)	Std. Pkg.
Ty-Rap® Stainless Steel Strapping on a Reel				
TYS1000	1,000-ft. of strap, 2 reels of 500 ft. each	0.31/7.87	200/889.60	1

Stainless steel ties of virtually any length can be produced from the 1,000-ft. reel in combination with the matching head.

Note: Use WT3S tool for tensioning and cutoff

A perfect mate with cable ties for tensioning



WT3S



DAS250

Cat. No.	Description	Std. Pkg.
Ty-Rap® Stainless Steel Cable Tie Installation Tools		
WT3S	Installs strapping ties	1
DAS250	Installs Multi-Lok™, ball lock, and roller bar lock stainless steel ties	

Lockable heads for stainless steel strapping



Cat. No.	Description	Std. Pkg.
Ty-Rap® Stainless Steel Strapping Locking Heads		
TYS5200H	Heads only for stainless strapping	50

Long-lasting anchor hold



Cat. No.	Description	Std. Pkg.
Ty-Rap® Stainless Steel Mounting Base		
TCS25	Mounting bases for stainless steel ties	50