



Actual

**Catalog Number:** 13610A  
**Product ID:** 7TAA131670R0001  
**UPC Number:** 78621088993  
**EAN Number:** 05415022357288  
**Status:** Active

Electric Hydraulic Pump with Shure-Stake Control, Hand or Foot Switch and Non-metallic Hose(Sold Separately)Required for Operation

- 120V., 60Hz, 10000 PSI Operating Pressure, Shure-Stake Mechanism
- Crimping terminals/splices/disconnects.

**North American Specifications (UNSPSC)**

UNSPSC	40151533 Hydraulic pumps
IGCC	6009 Hydraulic pumps
Brand Name	Color-Keyed
Type	Hydraulic Pump
Special Features	120V., 60Hz, 10000 PSI Operating Pressure, Shure-Stake Mechanism
Application	Crimping terminals/splices/disconnects.
Horsepower	1/2
Pressure Rating	10000 PSI
Mounting	7/16
Dimensions	8-1/2 Inch Length x 10-1/2 Inch Width x 16 Inch High

**European Specifications (ETIM)**

ETIM	EC001185 Hydraulic drive unit
Construction/operation	Electro-hydraulic pump

**Packaging**

Outer Quantity	1
Outer Dimensions (inches)	16x13x11.3
Weight Uom	5875 lbs. per 100

**Documents / Support Tools**

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website

**For further technical assistance, please contact us...**

ABB Installation Products - USA  
860 Ridge Lake Blvd.  
Memphis, TN 38120  
www.tnb.com

ABB Installation Products Technical Support  
MS 3B-50  
860 Ridge Lake Blvd.  
Memphis, TN 38120

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com