






Metal Clad Cable Termination Fittings & Accessories T&B Catalog Number:

UPC Number: Status: Description: STEX150 78621099683 Active

Star Teck Extreme hazardous location aluminum jacketed cable fitting hub size 1-1/2 inches. **Features**

	Patented powergrip grounding ring.
	Removable armor-stop for greater cable ranges.
	Patented elastomeric collar ring/busing for greater cable ranges.
	Built-in jacket stripping gauge on gland nut.
	Gland nut can be tightened with hammer and screwdriver.
Application	
	Provides means for passing armored, metal clad, jacketed cable through a bulkhead or enclosure in hazardous areas. (these fittings are suitable for hazardous areas when used with T&B sealing com pound).
	Form a mechanical grip and water and/or oil-resis- tant termination.
	Provide grounding continuity of cable armor.
General	
Material	Aluminum
Strip Length (inches)	1 3/4
Sealing Compound Required-Putty (grams)	80
Sealing Compound Required-Liquid (cc) Dimension Information	43
Hub Size (inches)	1 1/2
Dimension B (inches)	5.020
Dimension C (inches)	3.260
A1:Throat Diameter Minimum (w/Armor Stop)	0.958
A2:Throat Diameter Minimum (wo/Armor Stop)	1.273
Range Over Jacket -Minimum (inches)	1.150
Range Over Jacket -Maximum (inches)	1.625
Range Over Armor -Minimum (inches)	0.990
Range Over Armor -Maximum (inches)	1.465
Strip Length (inches)	1 3/4
Packaging	
T&B Inner Pack	1
Package in Units	4
T&B Sold in UOM	Each





 T&B Weight Per UOM
 20 lbs. per 100

 Application Support
 Available on Website

 Product Specifications & Overview
 Available on Website

 Notes
 UL Listed watertight NEMA Type 6P

 Certifications
 Yes

•

Certifications

File Nbr: E 82038

For further technical assistance, please contact us...

T&B Technical Support MS 3B-50 8155 T&B Blvd. Memphis, TN 38125 Hours: 7AM - 6PM CDT Monday-Friday Phone: (888) 862-3289 Fax: (901) 252-1321 Email:techsupport@thb.com

Thomas & Betts - USA 8155 T&B Blvd. Memphis, TN 38125 www.tnb.com