

Project/Location:


 Contractor:

 Date:

 Prepared by:

EF26/EF26DS/ EF26D Series

Surface Mount
Remote Fixture




FEATURES

- Cubic, vandal-resistant surface-mounted fixture
- Single, twin or double cube with center body
- Frosted polycarbonate cube
- CSA certified to C22.2 No. 141



DIMENSIONS

Dimensions are approximate and subject to change.



TYPICAL SPECIFICATIONS

Remote heads **EF26/EF26DS/EF26D Series** shall be comprised of one (single) or two (double or twin) 12W adjustable heads with halogen lamps. Each lamp shall be housed in an impact-resistant polycarbonate cube. The cube lens shall be frosted to diffuse the light.

Heads shall provide mounting holes for installation on a standard octagonal box.

The remote unit shall be the **Emergi-Lite®** model: _____.

WIRE GUARDS

460.0035-E	Wall Mount (EF26)
460.0032-E	Wall Mount (EF26D)
460.0031-E	Wall Mount (EF26DS)

REPLACEMENT LAMPS

MODEL	LAMP TYPE	VOLTAGE/WATTAGE
570.0016-E	Mini tungsten, wedge base	6V-9W
580.0079-E	MR16, flood	6V-10W
580.0100-E	MR16, LED	24V-6W

For the complete list, please see the lamp chart on pages 156 to 158

IN THE SAME FAMILY



DEL SERIES

P. 106-107

ORDERING INFORMATION

SERIES	LAMP STYLE	COLOUR	OPTIONS	LAMP STYLE/WATTAGE
EF26= single cube EF26D= double cube EF26DS= twin cube	Blank= tungsten Q= halogen M= MR16	Blank= factory white B= black	Blank= no options TP= tamper-proof screws* *690.0454-E= tamper-proof bit (sold separately)	-LA= MR16 LED, 6V-4W -LG= MR16 LED, 12V-4W -LI= MR16 LED, 12V-5W -LJ= MR16 LED, 12V-6W -LL= MR16 LED, 24V-4W -LM= MR16 LED, 24V-6W -LW= MR16 LED, 120V-4W -6V6W= MR16 halogen, 6V-6W -6V10W= MR16 halogen, 6V-10W -12V12W= MR16 halogen, 12V-12W -12V35W= MR16 halogen, 12V-35W -12V50W= MR16 halogen, 12V-50W -24V20W= MR16 halogen, 24V-20W -24V35W= MR16 halogen, 24V-35W -24V50W= MR16 halogen, 24V-50W -6V9W= tungsten, 6V-9W, wedge base -12V9W= tungsten, 12V-9W, wedge base -12V18W= tungsten, 12V-18W, wedge base -24V9W= tungsten, 24V-9W, wedge base -24V18W= tungsten, 24V-18W, wedge base -6V8W= halogen, 6V-8W, bi-pin -12V8W= halogen, 12V-8W, bi-pin -12V12W= halogen, 12V-12W, bi-pin -12V20W= halogen, 12V-20W, bi-pin -24V20W= halogen, 24V-20W, bi-pin -120V20W= MR16, GU10, 120V-20W -120V35W= MR16, GU10, 120V-35W

EXAMPLE: RSQBTV9W