

Catamount terminals



Catamount terminals – now in convenient, spillproof, re-usable packaging.

While poly bags keep their contents dry, they don't offer much other protection, and they aren't environmentally friendly. That's why Catamount terminals now come in sturdy plastic containers that safeguard the connectors inside against crushing and can be re-used or recycled when empty. ABB is always adding value to its products. With the introduction of a durable plastic container, the value of ABB's Catamount terminals has been significantly enhanced. No more lost or spilled terminals because of inadequate packaging.



Vinyl-insulated ring terminals



Cat. no.	Wire range (AWG)	Bolt hole (in.)	Pkg. qty.
TV18-6R-XV	22-16	#6	15
TV18-8R-XV	22-16	#8	15
TV18-10R-XV	22-16	#10	15
TV14-6R-XV	16-14	#6	15
TV14-8R-XV	16-14	#8	15
TV14-10R-XV	16-14	#10	15
TV10-8R-XV	12-10	#8	15
TV10-10R-XV	12-10	#10	15
TV10-14R-XV	12-10	¼	15



Vinyl-insulated fork terminals



Cat. no.	Wire range (AWG)	Bolt hole (in.)	Pkg. qty.
TV18-6F-XV	22-16	#6	15
TV18-8F-XV	22-16	#8	15
TV14-6F-XV	16-14	#6	15
TV14-8F-XV	16-14	#8	15
TV14-10F-XV	16-14	#10	15
TV10-8F-XV	12-10	#8	15
TV10-10F-XV	12-10	#10	15
TV10-14F-XV	12-10	¼	15



Vinyl-insulated butt splices



Cat. no.	Wire range (AWG)	Pkg. qty.
TV18-BS-XV	22-16	15
TV14-BS-XV	16-14	15
TV10-BS-XV	12-10	15

Vinyl-insulated butt splices kit



Cat. no.	Wire range (AWG)	Qty	Pkg. qty.
TV10-18-BS	22-18	5	15
	16-14	5	15
	12-10	5	15



Nylon-insulated wire joints



Cat. no.	Wire range (AWG)	Pkg. qty.
TN18-WJ-XV	22-18	15
TN14-WJ-XV	16-14	15
TN10-WJ-XV	12-10	15



Vinyl-insulated female disconnects – 250 series



Cat. no.	Wire range (AWG)	Pkg. qty.
TV18-250FD-XV	22-16	15
TV14-250FD-XV	16-14	15
TV10-250FD-XV	12-10	15



Vinyl-insulated male disconnects – 250 series



Cat. no.	Wire range (AWG)	Pkg. qty.
TV18-250MD-XV	22-16	15
TV14-250MD-XV	16-14	15
TV10-250MD-XV	12-10	15



Vinyl-insulated pin terminal



Cat. no.	Wire range (AWG)	Pkg. qty.
TV18-12PT-XV	22-16	15
TV14-12PT-XV	16-14	15
TV10-14PT-XV	12-10	15




Vinyl-insulated blade terminal



Cat. no.	Wire range (AWG)	Pkg. qty.
TV18-10BL-XV	22-16	15
TV14-10BL-XV	16-14	15
TV14-18BL-XV	16-14	15
TV10-10BL-XV	12-10	15


Catamount terminals



Vinyl-insulated double crimp locking fork 


Cat. no.	Wire range (AWG)	Pkg. qty.
TV18-10LFD-XV	22-16	15
TV18-6LFD-XV	22-16	15
TV18-8LFD-XV	22-16	15
TV14-10LFD-XV	16-14	15
TV14-6LFD-XV	16-14	15
TV14-8LFD-XV	16-14	15
TV10-10LFD-XV	12-10	15
TV10-6LFD-XV	12-10	15
TV10-8LFD-XV	12-10	15



Vinyl-insulated locking fork terminal 

Cat. no.	Wire range (AWG)	Pkg. qty.
TV18-10LF-XV	22-16	15
TV18-6LF-XV	22-16	15
TV18-8LF-XV	22-16	15
TV14-10LF-XV	16-14	15
TV14-6LF-XV	16-14	15
TV14-8LF-XV	16-14	15
TV10-10LF-XV	12-10	15
TV10-6LF-XV	12-10	15
TV10-8LF-XV	12-10	15



Non-insulated ring terminals 

Cat. no.	Wire range (AWG)	Pkg. qty.
T14-10R-XV	16-14	15
T14-8R-XV	16-14	15
T10-10R-XV	12-10	15
T10-14R-XV	12-10	15
T10-8R-XV	12-10	15



Non-insulated fork terminals 

Cat. no.	Wire range (AWG)	Pkg. qty.
T18-10F-XV	22-18	15
T18-8F-XV	22-18	15
T14-10F-XV	16-14	15
T14-8F-XV	16-14	15
T10-10F-XV	12-10	15
T10-14F-XV	12-10	15
T10-8F-XV	12-10	15



Vinyl fully insulated double crimp female disconnect 


Cat. no.	Wire range (AWG)	Pkg. qty.
TVF18-250FDD-XV	22-16	15
TVF14-250FDD-XV	16-14	15
TVF10-250FDD-XV	12-10	15



Vinyl fully insulated female disconnect 

Cat. no.	Wire range (AWG)	Pkg. qty.
TVF18-250FD-XV	22-16	15
TVF14-250FD-XV	16-14	15
TVF10-250FD-XV	12-10	15



Vinyl-insulated double crimp piggy-back disconnect 

Cat. no.	Wire range (AWG)	Pkg. qty.
TV18-250PDD-XV	22-16	15
TV14-250PDD-XV	16-14	15
TV10-250PDD-XV	12-10	15



Vinyl-insulated piggy-back disconnect 

Cat. no.	Wire Range (AWG)	Pkg. qty.
TV18-250PD-XV	22-16	15
TV14-250PD-XV	16-14	15
TV10-250PD-XV	12-10	15



Vinyl-insulated quick splice 

Cat. no.	Wire range (AWG)	Pkg. qty.
TV18-00QS-V	22-18	15
TV14-00QS-V	18-14	15
TV10-00QS-V	12-10	15



Vinyl-insulated double crimp female disconnect 

Cat. no.	Wire range (AWG)	Pkg. qty.
TV18-250FDD-XV	22-16	15
TV14-250FDD-XV	16-14	15
TV10-250FDD-XV	12-10	15

Catamount terminals



Nylon fully insulated female disconnect



Cat. no.	Wire range (AWG)	Pkg. qty.
TNF18-250FD-XV	22-16	15
TNF14-250FD-XV	16-14	15
TNF10-250FD-XV	12-10	15



Nylon fully insulated male disconnect



Cat. no.	Wire range (AWG)	Pkg. qty.
TNF-18-250MD-XV	22-16	15
TNF-14-250MD-XV	16-14	15
TNF-10-250MD-XV	12-10	15



Nylon fully insulated female bullet



Cat. no.	Wire range (AWG)	Pkg. qty.
TNF18-4FB-XV	22-16	15
TNF14-4FB-XV	16-14	15



Nylon fully insulated male bullet



Cat. no.	Wire range (AWG)	Pkg. qty.
TNF18-4MB-XV	22-16	15
TNF14-4MB-XV	16-14	15



Nylon fully insulated double crimp female disconnects



Cat. no.	Wire range (AWG)	Pkg. qty.
TNF-18-250FDD-XV	22-16	15
TNF-14-250FDD-XV	16-14	15
TNF-10-250FDD-XV	12-10	15



Nylon fully insulated double crimp male disconnect



Cat. no.	Wire range (AWG)	Pkg. qty.
TNF-18-250MDD-XV	22-16	15
TNF-14-250MDD-XV	16-14	15
TNF-10-250MDD-XV	12-10	15



Vinyl-insulated double crimp male disconnect



Cat. no.	Wire range (AWG)	Pkg. qty.
TV-18-250MDD-XV	22-16	15
TV-14-250MDD-XV	16-14	15
TV-10-250MDD-XV	12-10	15