Microlectric®

Meter Sockets



CO22-U Series


200 A (Main Lugs), 200 A per Position, Single Phase 120/240 V; Multiple Position Combination with Compartment with or without Breaker

Product Specifications

- Conductor range: Line: Single 1/2 in. stud to accommodate compression lugs (supplied by utility), Load: 6 AWG-250 kcmil
- · Aluminum tunnel type connectors for load sides
- For underground service only
- · Factory pre-bussed from main lugs to each position
- Internal locking system for covers
- Supplied with screw type sealing rings
- · Factory installed 2 pole circuit breaker, 10,000 A rms interrupting capacity
- Siemens Type "QJ" breaker
- With adjustable breaker plate for field installation of Square D–Type QBL and Eaton–Type ED breakers
- CO3009-KIT (Siemens), CO3009SD-KIT (Square D) and CO3409FB-KIT (Eaton) conductor kits available (breakers not included) see page D52
- Weatherproof Type 3R enclosure
- Primarily used: All Provinces
 Quebec only: As per Hydro-Québec spec (supplied with 22 kA Siemens breaker)



Note: Consult your Regional Sales Office for right-hand entry option.



Cat. No.	Туре	Description	Position	Dimensions (in.)			Weight Each	
				Н	W	D	lb.	kg
Left-Hand Entry								
C022-U	Underground only	2 gang with blank compartment, provision for Siemens 2 x (QJ), 200 A 2 pole 10 kA rated circuit breakers		30	26-1/4	5-1/2	60	27.21
C022-200-U		2 gang with blank compartment, c/w Siemens 2 x QJ 200 A 2 pole 10 kA rated circuit breakers	3					
C022-200HI-U		2 gang with blank compartment, c/w Siemens 2 x QJH 200 A 2 pole 22 kA rated circuit breakers						
C023-U		3 gang with blank compartment, provision for Siemens 3 x (QJ), 200 A 2 pole 10 kA rated circuit breakers			35		80	36.29
C023-200-U		3 gang with blank compartment, c/w Siemens 3 x QJ 200 A 2 pole 10 kA rated circuit breakers						
C023-200HI-U		3 gang with blank compartment, c/w Siemens 3 x QJH 200 A 2 pole 22 kA rated circuit breakers						
C024-U		4 gang with blank compartment, provision for Siemens 4 x (QJ), 200 A 2 pole 10 kA rated circuit breakers			43-3/4		100	45.36
C024-200-U		4 gang with blank compartment, c/w Siemens 4 x QJ 200 A 2 pole 10 kA rated circuit breakers						
C024-200HI-U		4 gang with blank compartment, c/w Siemens 4 x QJH 200 A 2 pole 22 kA rated circuit breakers						



