

PHILIPS

InteGrade

LED

InteGrade accessories



Datasheet

InteGrade LED system

Compact linear LED lighting for ultimate shopping experience

Thanks to a range of accessories, engine lengths, fixtures, color temperatures and Constant Voltage LED power drivers, the InteGrade LED system offers modular approach for maximum design flexibility. This enables a vast variety of innovative systems with style and functionality according the needs of the stores. The accessory table shows which accessories are suitable for your InteGrade LED system.

December 2020

Ordering data

Commercial product name	EOC	12NC	Box quantity
InteGrade power cable 1m(39") black	8718291 218128 00	9290 006 41014	24
InteGrade power cable 2.5m(98") black	8718291 221449 00	9290 006 41114	24
InteGrade cable 1m(39") black angle	8718291 221364 00	9290 006 44614	24
InteGrade cable 2.5m(98") black angle	8718291 221463 00	9290 006 44814	24
InteGrade power cable 1m(39") white	8718291 221401 00	9290 006 45614	24
InteGrade power cable 2.5m(98") white	8718291 221487 00	9290 006 44514	24
InteGrade cable 1m(39") white angle	8718291 221425 00	9290 006 44714	24
InteGrade cable 2.5m(98") white angle	8718291 221500 00	9290 006 44914	24
InteGrade power cable 6m white	8718696 824375 00	9290 016 24806	12
InteGrade power cable 6m black	8719514 294943 00	9290 028 59106	12
InteGrade power cable 1.85m white	8718696 824450 00	9290 016 25206	96
InteGrade power cable 0.7m white	8718696 824474 00	9290 016 25306	96
InteGrade extension cable 1.5m(59") black	8718291 707257 00	9290 008 74413	24
InteGrade spacer cable 0.5m black	8718291 221524 00	9290 006 45014	24
InteGrade spacer cable 0.5m white	8718291 221548 00	9290 006 45114	24
InteGrade spacer cable M 0.7m 5.5c black	8718696 824351 00	9290 016 24706	24
InteGrade spacer cable 0.3m black	8718696 824412 00	9290 016 25006	24
InteGrade spacer cable 113mm white	8718696 824436 00	9290 016 25106	24
InteGrade spacer cable 50mm T a-a	8719514 281110 00	9290 021 82006	24
InteGrade spacer cable 0.2m T s-s	8719514 281141 00	9290 021 82106	24
InteGrade spacer cable 0.5m T a-s	8719514 281172 00	9290 021 82206	24
InteGrade spacer cable 1.0m T a-s	8719514 281202 00	9290 021 82406	24
InteGrade spacer cable 1.5m T a-s	8719514 281233 00	9290 021 82506	24
InteGrade spacer cable 2m T a-s	8719514 281264 00	9290 021 99306	24
InteGrade spacer cable 2.5m T a-s	8719514 281295 00	9290 021 99406	24
InteGrade Y cable black	8718291 707233 00	9290 008 74313	24
InteGrade magnet for M style profile	9718291 707271 00	9290 008 71413	100
InteGrade mounting clip shelf arm V2	8718696 446454 00	9290 009 57806	100
InteGrade mounting clip under shelf	8718291 218814 00	9290 006 43903	100
InteGrade mounting clip for T style prof	8718291 676508 00	9290 008 53213	100
InteGrade snap-in clip for fixtures	8719514 281325 00	9290 021 99706	100
InteGrade screw clip_Tstyle prof and fix	8719514 281356 00	9290 021 99806	100
InteGrade engine clip shelf arm G2	8718696 657102 00	9290 015 16006	100
InteGrade engine mounting clip G2	9718696 657126 00	9290 015 16106	100
InteGrade mounting clip canopy	8718696 716304 00	9290 015 71106	100
InteGrade engine clip mullion center	8718696 824535 00	9290 016 24406	100
InteGrade engine clip mullion side	8718696 824559 00	9290 016 24506	100
InteGrade engine clip magnetic	8718696 824573 00	9290 016 24606	100
InteGrade profile 875mm(34")	8718291 219538 00	9290 006 43413	48
InteGrade profile 1175mm(46")	8718291 219552 00	9290 006 43313	48
InteGrade profile 2000mm(79")	8718291 257899 00	9290 006 54413	48
InteGrade profile 2000mm(79") L style	8718291 257912 00	9290 006 54513	48
InteGrade profile 2000mm(79") F style	8718291 227892 00	9290 006 54313	24
InteGrade profile 2000mm(79") T style CTR	8718291 676461 00	9290 008 53013	16
InteGrade profile 2000mm(79") T style SD	8718291 676485 00	9290 008 53113	16
InteGrade prof 2000mm T style CTR G2	8719514 281387 00	9290 021 99506	16
InteGrade prof 2000mm T style SD G2	8719514 281400 00	9290 021 99606	16
InteGrade profile 2356mm (93") M style	8718291 703198 00	9290 008 71313	36
InteGrade connector	8718696 462157 00	9290 009 59106	500
InteGrade engine lock inline	8718291 219514 00	9290 006 43713	100
InteGrade rotational bracket	8718291 707691 00	9290 008 74613	100

Compatibility with InteGrade engines and fixtures

12NC	Product name	Canopy engine	Canopy with profile	shelf engine	Shelf with profile	Vertical engine	Vertical fixtures G4	Vertical engine with profiles	Serve over cooler	Island Freezer	Fully/half height freezer	Underwell freezer	Plug & Play (PP) transformers	Remark
929000641014	InteGrade power cable 1m(39") black	•	•	•	•	•	•	•	•	•	•	•		
929000641114	InteGrade power cable 2.5m(98") black	•	•	•	•	•	•	•	•	•	•	•		
929000644614	InteGrade cable 1m(39") black angle			•	•					•	•	•		
929000644814	InteGrade cable 2.5m(98") black angle			•	•					•	•	•		
929000645614	InteGrade power cable 1m(39") white	•	•	•	•	•	•	•	•	•	•	•		
929000644514	InteGrade power cable 2.5m(98") white	•	•	•	•	•	•	•	•	•	•	•		
929000644714	InteGrade cable 1m(39") white angle			•	•					•	•	•		
929000644914	InteGrade cable 2.5m(98") white angle			•	•					•	•	•		
929001624806	InteGrade power cable 6m white			•	•					•		•		
929002859100	InteGrade power cable 6m black			•	•					•		•		NEW
929001625206	InteGrade power cable 1.85m white	•	•	•	•	•	•	•	•	•	•	•		
929001625306	InteGrade power cable 0.7m white			•	•									
929000874413	InteGrade extension cable 1.5m(59") black			•	•									
929001650106	InteGrade power cable 3m black angle			•	•									
929000645014	InteGrade spacer cable 0.5m black			•	•				•	•		•	•	
929000645114	InteGrade spacer cable 0.5m white			•	•				•	•		•	•	
929001625306	InteGrade spacer cable M 0.7m 5.5c black			•	•								•	
929001625006	InteGrade spacer cable 0.3m black angle			•	•				•	•		•	•	
929001625106	InteGrade spacer cable 113mm white			•	•				•	•		•	•	
929002182006	InteGrade spacer cable 50mm T a-a	•	•	•	•				•	•		•	•	NEW (T= transparant)
929002182106	InteGrade spacer cable 0.2m T s-s	•	•	•	•				•	•		•	•	NEW (T= transparant)
929002182206	InteGrade spacer cable 0.5m T a-s	•	•	•	•				•	•		•	•	NEW (T= transparant)
929002182406	InteGrade spacer cable 1.0m T a-s			•	•				•	•		•	•	NEW (T= transparant)
929002182506	InteGrade spacer cable 1.5m T a-s			•	•				•	•		•	•	NEW (T= transparant)
929002199306	InteGrade spacer cable 2m T a-s			•	•				•	•		•	•	NEW (T= transparant)
929002199406	InteGrade spacer cable 2.5m T a-s			•	•				•	•		•	•	NEW (T= transparant)
929000874313	InteGrade Y cable black			•	•								•	
929000871413	InteGrade magnet for M style profile		•		•									
929000957806	InteGrade mounting clip shelf arm V2				•									
929000643903	InteGrade mounting clip under shelf				•									
929000853213	InteGrade mounting clip for T style prof						•	•			•			
929002199706	InteGrade snap-in clip for fixtures						•							NEW
929002199806	InteGrade screw clip_Tstyle prof and fix						•	•						NEW
929001516006	InteGrade engine clip shelf arm G2			•										
929001516106	InteGrade engine mounting clip G2			•										
929001571106	InteGrade mounting clip canopy	•								•		•		
929001624406	InteGrade engine clip mullion center					•								
929001624506	InteGrade engine clip mullion side					•								
929001624606	InteGrade engine clip magnetic			•										
929000643413	InteGrade profile 875mm(34")		•		•					•		•		
929000643313	InteGrade profile 1175mm(46")		•		•					•		•		
929000654413	InteGrade profile 2000mm(79")		•		•				•	•		•		
929000654513	InteGrade profile 2000mm(79") L style		•		•	•	•	•		•		•		
929000654313	InteGrade profile 2000mm(79") F style		•		•					•		•		
929000853013	InteGrade prof 2000mm(79") T style CTR					•	•	•			•			will be Phased out
929000853113	InteGrade profile 2000mm(79") T style SD					•	•	•			•			will be Phased out
929002199506	InteGrade prof 2000mm T style CTR G2						•							NEW
929002199606	InteGrade prof 2000mm T style SD G2						•							NEW
929000871313	InteGrade profile 2356mm (93") M style		•		•					•		•		
929000959106	InteGrade connector		•		•	•	•	•	•			•	•	
929000643713	InteGrade engine lock inline		•		•				•		•	•		
929000874613	InteGrade rotational bracket		•											