

MPHB-250

Versatile parts for easy installation



NAME:	
TYPE:	
DATE:	
NOTES:	

SPECIFICATIONS

PRODUCT DETAILS: Ideal for open ceilings with no insulation, soffits, new constructions or acoustic tiles

Adjustable mounting bars included, allows for installation between 13.00" (320mm) and 26.00"(660mm) openings

- Product codes
- MPHB-250 : 2.50" (63.50mm) Hole Diameter
 - MPHB-300 : 3.25" (82.55mm) Hole Diameter
 - MPHB-350 : 3.875" (98.42mm) Hole Diameter
 - MPHB-450 : 4.625" (117.47mm) Hole Diameter
 - MPHB-500 : 5.625" (142.87mm) Hole Diameter
 - MPHB-600 : 6.50" (165.10mm) Hole Diameter
 - MPHB-800 : 8.25" (210.00mm) Hole Diameter
 - MPHB-1000 : 10.00" (254.00mm) Hole Diameter

APPLICATIONS

Versatile adjustable mounting plate allows for installation of all models of NDR recessed lighting products. Refer to our Mounting Plate Compatibility Chart to ensure the proper mounting plate is selected.

DIMENSIONS

