

7.5 kW
POWERPACT
Automatic Home
Standby Generator

GENERAC®



The Most Affordable Home Standby Generator on the Market

7.5 kW AUTOMATIC STANDBY GENERATOR

THINK YOU CAN'T AFFORD AN AUTOMATIC STANDBY GENERATOR? *YOU CAN.*

Generac has engineered a home standby generator that makes residential backup power more affordable than ever, backed with the quality and reliability that makes Generac the leader in standby power. If you only need to protect your essential circuits and thought a portable generator was the best option for your money, compare the benefits of the Powerpact standby generator.

COVER ALL YOUR ESSENTIAL CIRCUITS:



TELEVISION



COMPUTER



LIGHTS



SUMP PUMP



REFRIGERATOR



FURNACE



AIR CONDITIONER



FEATURES



3 Year Limited Warranty for automatic standby generators.



True Power™ Technology delivers best-in-class power quality with less than 5 percent total harmonic distortion for clean, smooth operation of sensitive electronics and appliances.



24/7•365 Customer Support Team standing by all-day every-day from our headquarters in Wisconsin to answer any questions you might have.



Mobile Link™ Remote Monitoring allows you to monitor the status of your generator from anywhere in the world using a smartphone, tablet, or PC. Easily access information such as the current operating status, and the generators maintenance schedule. Connect your account to your authorized service dealer for fast, friendly and convenient assistance. *(Sold Separately). (Available in US only).*

POWERPACT VS. PORTABLE

FEATURE	7.5KW POWERPACT	7000 Watts PORTABLE GENERATOR
Protection	Automatic 24/7 hands-free operation	Manual start-up
Fuel	Continuous LP or natural gas, easy field fuel conversion	Refuel with gasoline as needed
Convenience	Permanently installed, always ready	Set up for every outage with extension cords
Weather Proof	Galvaneel steel enclosure sits outside as close as 18" to the home	Not recommended to run in the rain

7 out of every 10 homeowners choose Generac when investing in home backup power.

7.5 kW POWERPACT

AUTOMATIC HOME STANDBY GENERATOR



SPECIFICATIONS (LP/NG)	7.5 / 6 kW
Generator / 50 Amp, 8-Circuit Transfer Switch Model #	6998
Voltage (Single Phase)	240
Rated Maximum Continuous Load Current - 240 Volts	31.25 / 25
Engine/Alternator RPM	3600
Engine	Generac OHV 420cc
Fuel Consumption @ 1/2 Load NG cu. ft/hr (m3/hr)	73 (2.07)
Fuel Consumption @ Full Load - NG cu. ft/hr (m3/hr)	117 (3.31)
Fuel Consumption @ 1/2 Load - LPG cu. ft/hr (gal/hr)	31.6 (0.87)
Fuel Consumption @ Full Load - LPG cu. ft/hr (gal/hr)	51.6 (1.42)
Quiet-Test Mode	No
db(A) at Exercise	69
db(A) at Normal Operating Load	69
Enclosure	Steel
Enclosure Color	Bisque
Warranty	3-Year Limited
Dimensions (L" x W" x H")	36 x 27 x 35
Weight (lbs.) (Steel/Aluminum)	280

*Rating definitions - Standby: Applicable for supplying emergency power for the duration of the utility power outage. No overload capability is available for this rating. (All ratings in accordance with BS5514, ISO3046 and DIN6271). * Maximum wattage and current are subject to and limited by such factors as fuel Btu content, ambient temperature, altitude, engine power and condition, etc. Maximum power decreases about 3.5 percent for each 1,000 feet above sea level and also will decrease about 1 percent for each 12° C (10° F) above 15.5° C (60°F). Not for sale in California.

Nationwide Dealer Service Network

Generac's commitment to service includes scheduled maintenance programs, warranty assistance and emergency service to ensure that Generac customers are never left powerless. The largest nationwide dealer network has factory-trained technicians on staff and maintains large inventories of Generac parts, components and accessories. Find a dealer near you at generac.com.

GENERAC®