# Smarter spaces, lower costs, more control



Legrand provides the most expansive offering of lighting controls for managing delivery of light and data. Wattstopper's unmatched portfolio of lighting controls enables sustainability and increases energy efficiency.

What makes Wattstopper's dimmers so special? They simply work. We have a solution for every lamp, every load, in every setting imaginable.

From saving energy to setting the mood, our extensive line of easy-to-use dimming solutions delivers an unmatched level of control wherever you live, work, and play. Visually appealing and easy to install, they are a great way to enhance a room's ambiance while reducing power consumption.





#### Dimmers to handle virtually every type of lamp and load.





CFL/LED DIMMERS
The smart choice for these popular lamps



MULTI-LOCATION DIMMERS More dimming control meets more style



LED SYSTEMS
Stylish solutions for the latest lighting technologies



INCANDESCENT DIMMERS
A stylish solution for standard lamps



FAN SPEED CONTROLS
A cool way to control airflow in any room

#### Color Designations\*

**W** White

LA Light Almond

Ivory

**BK** Black

- Brown

**GRY** Gray

NI Nickel

AB Antique Brass

DB Dark Bronze



















## THE UNIVERSAL DIMMER THAT SIMPLY WORKS



Our new radiant dimmers are all about style. But thanks to our innovative Tru-Universal technology, they radiate simplicity as well. In fact, the radiant Tru-Universal Dimmer is the only dimmer that works with virtually every lamp and load. It's not just the technology that makes radiant the perfect choice, but also its user-friendly features:

- Wider slide controller for easier dimming operation
- Ergonomic slider grip for more intuitive finger control
- Larger paddle switch that is easy to see and use
- Sleek, modern design that matches today's style
- A locator LED glows when OFF to make the dimmer easier to find in the dark





Since only one dimmer is needed for virtually every lamp and load, it reduces the number of SKUs needed for stocking or hauling around.






With interchangeable faces in popular colors like White, Ivory, and Light Almond, there is no longer a need to stock all colors—they are easily changed on-site.

## FAST, COST-EFFECTIVE INSTALLATION

Ganging commercial dimmers used to require costly, customized wall plates that couldn't be ordered until a configuration was finalized. Titan® Series Dimmers change everything. Unlike the others, Titan Dimmers provide a complete solution that saves time and money and offers endusers a superior, more convenient, and better-looking multi-gang installation.









#### radiant® Dimmers













# RHKIT Interchangeable Face Plate HMKIT Multi-location Dimmer, Interchangeable Face Plate HDHKIT Multi-location De-hummer, Fan Speed Control, Interchangeable Face Plate HMRKIT Multi-location Remote Dimmer, Interchangeable Face Plate COLOR Ivory, White, Light Almond, Black, Brown, Gray, Nickel, Antique Brass, Dark Bronze



5



#### TRU-UNIVERSAL DIMMERS

- Work with virtually every lamp and load
- Self-calibrate to match lamp type
- Allow you to dial in the performance of the lamp you choose

WWW.LEGRAND.US/WATTSTOPPER

<sup>\*</sup>See color designations on page 2



### TITAN® SERIES DIMMERS

- Capacity to handle large loads
- Included screwless wall plate components make it easy to assemble multi-gang configurations, saving money and time
- Optional built-in label holder enables instant circuit identification; looks clean and professional
- Power-failure memory retains presets through power outages

### Titan® Series Dimmers











PART NO.*	DESCRIPTION	COLOR	RATING
CD1103P	Incandescent		40-1100W
CD2003P	Incandescent		40-2000W
CDLV703P	Magnetic Low Voltage		40-700VA
CDLV1103P	Magnetic Low Voltage		40-1600VA
CDFB83P	Two-Wire Fluorescent		0.33-8A
CDFB163P	Two-Wire Fluorescent		0.33-16A
CDFB103P277	Two-Wire Fluorescent	White, Ivory, Gray, Black, Light Almond, Brown	0.33-16A
CD3FB163P	Three-Wire Fluorescent		0.33-16A
CD3FB103P277	Three-Wire Fluorescent		0.33-10A
CD4FB	Four-Wire 0-10V, Fluorescent		Up to 60 ballasts
CD4FBL	Four-Wire 0-10V, Fluorescent		30mA
CD4FBL3P	Four-Wire 0-10V, Fluorescent		30mA
CDSC6	Fan Speed Control		0.33-6A

<sup>\*</sup>See color designations on page 2





# STYLISHLY SIMPLE DIMMING SOLUTIONS



### **Multi-location Touch Dimmers**











PART NO.*	DESCRIPTION	COLOR	RATING
TDA603	Master Dimmer w/ Neutral Single Pole/3-Way		120V; 25-600W
TD603	Incandescent Master Dimmer Single Pole/3-Way	White, Ivory, Almond,	120V; 40-600W
TDFC1A	Fan Speed Control Master Single Pole/3-Way	Light Almond, Gray, Black	120V; 1.5A
TDR	Remote		120V







## MULTI-LOCATION TOUCH DIMMERS

- Easily dim from multiple locations
- Change 3-Way and 4-Way switches to dimming
- Fan Speed Control also available







FOR EVERY SETTING

WWW.LEGRAND.US/WATTSTOPPER 7



#### TOGGLE PRESET DIMMERS

- Convenient preset dimming control
- Combines
   ON/OFF toggle
   with separate
   dimming wheel
   for light-level
   control
- Matches appearance of standard toggle switches

## **Toggle Dimmers**












PART NO.*	DESCRIPTION	COLOR	RATING
T1000	Incandescent Single Pole, Non-Preset	Brown, Ivory, Light Almond, White	120V; 1000W
T1003	Incandescent 3-Way, Non-Preset		
T600	Incandescent Single Pole, Non-Preset	Brown, Ivory, Light Almond, White	120V; 600W
TLV603	Magnetic Low Voltage 3-Way, Non-Preset	Ivory, Light Almond, White	120V; 600VA
TD1103P	Incandescent Single Pole/3-Way, Preset	Black, Brown, Ivory, Light Almond, White	120V; 1100W
TD703P			120V; 700W
TDFB83P	Fluorescent Single Pole/3-Way, Two Wire, Preset	Black, Brown, Ivory, Light Almond, White	120V; 8A
TSC5	Fan Speed Control Adjustable Trim, Non-Preset	Ivory, Light Almond, White	120V; 5A
TDDH163P	Fan Speed Control De-hummer	Black, Brown, Ivory, Light Almond, White	120V; 1.6A
TDCL453P	CFL/LED Single Pole/3-Way, Preset	Black, Brown, Ivory, Light Almond, White	120V; 450W CFL/LED; 700W Incandescent

<sup>\*</sup>See color designations on page 2





# DIMMING SOLUTIONS FOR EVERY NEED AND BUDGET

#### Wide Slide Dimmers












DESCRIPTION	COLOR	RATING	
Incandescent Single Pole, Non-Preset	Three Interchangeable Face Colors: Ivory, White, Light Almond	120V; 1000W	
Incandescent Single Pole, Non-Preset	Three Interchangeable Face Colors: Ivory, White, Light Almond	120V; 1100W	
Incandescent Single Pole/3-Way, Preset	Three Interchangeable Face Colors: Ivory, White, Light Almond		
Incandescent Single Pole, Non-Preset	Three Interchangeable Face Colors: Ivory, White, Light Almond		
Incandescent	Three Interchangeable Face Colors: Ivory, White, Light Almond	120V; 700W	
Single Pole/3-Way, Preset	White		
CFL/LED/Incandescent Single Pole, Non-Preset	Three Interchangeable Face Colors: Ivory, White, Light Almond		
	White	120VAC; 450W	
CFL/LED/Incandescent Single Pole/3-Way, Preset	Three Interchangeable Face Colors: Ivory, White, Light Almond		
	White		
LED/Fluorescent	Three Interchangeable Face Colors: Ivory, White, Light Almond	0-10V	
Single Pole/3-Way, Preset	White		
Fan Speed Control Variable Speed, Preset	White	120V; 5A	
Fan Speed Control De-hummer, Single Pole	Three Interchangeable Face Colors: Ivory, White, Light Almond	120V; 1.6A	
	White	,	
Magnetic Low Voltage Single Pole, Non-Preset	Three Interchangeable Face Colors: Ivory, White, Light Almond		
Magnetic Low Voltage Single Pole/3-Way, Preset	Three Interchangeable Face Colors: Ivory, White, Light Almond	120V; 700VA	
DESCRIPTION		COLOR	
Interchangeable Face Plate, Non-Preset		Black, Brown, Ivory, Light Almond, White	
Interchangeable Face Plate, Preset			
	Incandescent Single Pole, Non-Preset  Incandescent Single Pole, Non-Preset  Incandescent Single Pole/3-Way, Preset  Incandescent Single Pole, Non-Preset  Incandescent Single Pole/3-Way, Preset  CFL/LED/Incandescent Single Pole, Non-Preset  CFL/LED/Incandescent Single Pole/3-Way, Preset  LED/Fluorescent Single Pole/3-Way, Preset  Fan Speed Control Variable Speed, Preset  Fan Speed Control De-hummer, Single Pole  Magnetic Low Voltage Single Pole/3-Way, Preset  Magnetic Low Voltage Single Pole/3-Way, Preset	Incandescent   Single Pole, Non-Preset   Nory, White, Light Almond	

<sup>\*</sup>See color designations on page 2





#### **SCREWLESS WALL PLATES**

- Premium finishes that stand up to constant use
- Hidden screws create a sleek, seamless accent
- Available in single- and multiple-gang configurations



### WIDE SLIDE DIMMERS

- Available in preset and slide-to-OFF models
- 3 interchangeable face plates in one package
- Faces snap easily into place and match any décor
- Operational in single-pole and 3-Way applications

WWW.LEGRAND.US/WATTSTOPPER



### LS SERIES DIMMERS

- Ergonomic design and solid, quality material
- Sleek, sculpted, contemporary design
- Patented Snap-In Light Module for easy nighttime visibility (sold separately)

#### LS Series Dimmers











PART NO.*	DESCRIPTION	COLOR	RATING
LS1000	Incandescent Single Pole, Non-Preset	Black, Brown, Ivory, Light Almond, White	120V; 1000W
LS1000P	Incandescent Single Pole, Preset		
LS1003P	Incandescent 3-Way, Preset		
LS600	Incandescent Single Pole, Non-Preset	Black, Brown, Ivory, Light Almond, White	
LS600LWV	Incandescent Lighted, Single Pole, Non-Preset	White	120V; 600W
LS600P	Incandescent Single Pole, Preset	Black, Brown, Ivory, Light Almond, White	
LS603P	Incandescent 3-Way, Preset		
LS603PLWV	Incandescent Lighted, 3-Way, Preset	White	
LSCL450	<b>CFL/LED/Incandescent</b> Single Pole, Non-Preset	Black, Brown, Ivory, Light Almond, White	120VAC; 450W CFL/LED;
LSCL453P	CFL/LED/Incandescent 3-Way, Preset		700W Incandescent
LSCLDC163P	CFL/LED/Incandescent Single Pole/3-Way, Preset Dimmer with Single Pole/3-Way, 3-Speed De-hummer Fan Control	Black, Brown, Ivory, Light Almond, White	1.6A (Fan Control); 120VAC, 150W CFL/ LED; 300W Incandescent (Dimmer)
LSLV600	Magnetic Low Voltage Single Pole, Non-Preset	Black, Brown, Ivory, Light Almond, White	120V; 600VA
LSLV600P	Magnetic Low Voltage Single Pole, Preset		
LSLV603P	Magnetic Low Voltage 3-Way, Preset		
LSDC16V	Fan Speed Control 3-Speed De-hummer Fan Speed Control, Non-Preset with Single Pole Incandescent Dimmer	Brown, Ivory, Light Almond, White	1.6A (Fan Control); 120V;
LSDC16PV	Fan Speed Control 3-Speed De-hummer Fan Speed Control, Preset with Single Pole Incandescent Dimmer	Brown, Black	300W Incandescent (Dimmer)
LSDH16V	Fan Speed Control 4-Speed De-hummer, Non-Preset	Black, Brown, Ivory, Light Almond, White	1.6A
LSSC5	Fan Speed Control Single Pole with Adjustable Trim, Non-Preset		5A
LSSC5P	Fan Speed Control Single Pole with Adjustable Trim, Preset		


<sup>\*</sup>See color designations on page 2

## **Rotary Series Dimmers**



PART NO.*	DESCRIPTION	COLOR	RATING
R1000V	Incandescent Single Pole with RFI Filtering, Non-Preset	Ivory, Light Almond, White 1	120V; 1000W
R1000PV	Incandescent Single Pole with RFI Filtering, Preset		
R1003PV	Incandescent 3-Way with RFI Filtering, Preset		
R600V	Incandescent Single Pole with RFI Filtering, Non-Preset		
R600PV	Incandescent Single Pole with RFI Filtering, Preset	lvory, Light Almond, White	
R600PLTKV	Incandescent Single Pole with RFI Filtering, Preset	Three Interchangeable Face Colors: 120V; 600W Ivory, White, Light Almond	120V; 600W
R603PV	Incandescent 3-Way with RFI Filtering, Preset	Ivory, Light Almond, White	
R603PLTKV		Three Interchangeable Face Colors: Ivory, White, Light Almond	

<sup>\*</sup>See color designations on page 2







- Full-range rotary dimming
- Ground lead included on all models
- All models fit standard toggle wall plate

#### **DR Series Dimmers**












PART NO.*	DESCRIPTION	COLOR	RATING
DRCL453P	<b>CFL/LED</b> Single Pole/3-Way, Preset	Black, Brown, Ivory, Light Almond, White	120V; 450W CFL/LED; 700W Incandescent
DR703PV	Incandescent Single Pole/3-Way with Pilot Light, Preset	Black, Brown, Ivory, Light Almond, White	120V; 700W
DRLV1103P	Magnetic Low Voltage Single Pole/3-Way with Pilot Light, Preset	Black, Brown, Ivory, Light Almond, White	120V; 1100VA
DRLV703P			120V; 700VA
DRDH163PV	Fan Speed Control 3-Speed De-hummer Fan Speed Control with Single Pole/3-Way, Backlit Speed Indication, Preset	Black, Brown, Ivory, Light Almond, White	120V; 1.6A
DRSC53PV	Fan Speed Control Continuously Variable, Single Pole/3-Way, Preset		120V; 5A

<sup>\*</sup>See color designations on page 2







#### **DR SERIES DIMMERS**

- Contemporary style
- Illuminated knob indicates light level
- Snap-In LED modules make dimmers easy to find at night (sold separately)
- Available for incandescent and low-voltage lighting



designed to be better  $^{\scriptscriptstyle{\text{TM}}}$ 



Wattstopper, North America www.legrand.us/wattstopper