


UY Yellow IDC Jellybean 2-Wire Butt Splice

Traditionally used in landline telephone applications, these IDC insulation displacement splice connectors can be used to splice, tap or repair damaged many types of low voltage conductors in voice and data applications. Do not strip individual conductors before crimping.

- Internal moisture-resistant sealant protects wires from corrosion (indoor/outdoor use)
- · Quick, one-step splicing insert unstripped conductors and crimp
- Use with solid copper single-conductor wire, 22-26 AWG
- Maximum insulated O.D. of .060 in. (1.52 mm)
- Permanent connection- once crimped they cannot be reused
- Use 1 or 2 ports as needed:
- 1 port for terminating the end of a unused wire as an end cap
- 2 ports for repairing a broken wire or extending a single run
- Only crimp with a parallel jaw crimp tool
- Recommended crimp tool: 33-719

Part No.	Qty
85-950	25/Card



Also available:



www.idealind.com © IDEAL INDUSTRIES, INC.