DELIVERS PONER PERFORMANCE



lein brings over 160 years of the quality, durability and expertise in hand tools to battery-operated tools.

This new line of battery-operated cable cutters, crimpers and impact wrench are engineered to help linemen work more efficiently by reducing time and effort on the job.

All with the performance and durability professionals expect from Klein.

DEWAL

7-TON COMBINATION CABLE CUTTER/ CRIMPERS

One tool with 6 heads depending on what the job requires. 7-ton hydraulic force crimps a larger capacity faster than similar models on the market.

· Compatible with industry standard W-style dies

Cul

- Two work lights
- Replacement blades available
- Green light indicator to confirm a good crimp has been made
- Powered by DeWALT lithium-ion batteries





Card and and ACSR

1 EHS

GRADE 8 Bolts

GEAR-DRIVEN CABLE CUTTERS

KLEIN TOOLS

KLEIN TOOLS







EHS





Cuts copper and aluminum or ACSR cable in both open and closed jaw styles. The open jaw style is ideal when working in tight spaces while the closed jaw style provides higher cutting capacity up to 1/2" EHS.

- Two work lights
- Replacement blades available
- Safety Lockout Switch
- Powered by DeWALT lithium-ion batteries



12-TON Crimper



Designed for professional cable crimping applications, this tool provides 12 tons of force to get the job done fast. It crimps copper, aluminum and ACSR. The head rotates 360° for position flexibility. Compatible with industry standard U-Style dies. Available with battery, case and charger or just the crimper.

• Green light indicator to confirm a good crimp has been made

KLEIN

- Four work lights
- Safety Lockout Switch
- Powered by DeWALT lithium-ion batteries





For professional impact fastening and drilling applications. The impact function makes this tool particularly useful for driving fasteners in wood, metal and concrete.

- 7/16" (11 mm) Quick-Release Chuck
- Up to 500 ft-lbs of max torque
- 0 –1900 RPM variable speed trigger
- Safety Lockout Switch
- Powered by DeWALT lithium-ion batteries

12-Ton Crimper							
Cat. No.	Description	Cable Capacity (MCM)					
		Cu	AI	ACSR			
BAT20-12T1651	Crimper, C-Style Head (includes case, two 4 Ah batteries & charger)	8 AWG to	8 AWG to 750 MCM	556 MCM			
BAT20-12T165	Crimper, C-style head (includes a case)	750 MCM					

High-Torque Impact Wrenches

Cat. No.	Description
BAT20-7161	Impact Wrench, 7/16" (includes bag, two 4 Ah batteries & charger)
BAT20-716	Impact Wrench, 7/16"

Gear-Driven Cable Cutters

KLEIN TOOLS

Cat. No.	Description		Cable Capacity (MCM)			Replacement
		Cu	AI	ACSR	EHS	Blades
New Next Generation						
BAT20-GD1	EHS Closed-Jaw Cable Cutter (includes bag, two 2 Ah batteries & charger)	750	1500	1590	1/2"	BAT20-GD4BEHS
BAT20-GD14H	EHS Closed-Jaw Cable Cutter (includes bag, two 2 Ah batteries & charger)					
BAT20-GD10	Cu/Al Closed-Jaw Cable Cutter (includes bag, two 2 Ah batteries & charger)	1000*	1500		-	BAT20-GD4BAC
While Supplies Last						
BAT20-G1	ACSR, Closed-Jaw Cable Cutter (includes bag, two 2 Ah batteries & charger)	600	1500	1590	-	BAT20-G4
BAT20-G2	ACSR, Open-Jaw Cable Cutter (includes bag, two 2 Ah batteries & charger)	400	900	795	_	BAT20-G5
BAT20-G10	Cu/AI Closed-Jaw Cutter (includes bag, two 2 Ah batteries & charger)	750	1500	-	-	BAT20-G8
BAT20-G7	Cu/Al Open-Jaw Cutter (includes bag, two 2 Ah batteries & charger)	600	1000	-		BAT20-G9
					1000	MCM is soft copper grade only

7-Ton Combination Cable Cutter/Crimpers[†]

Oct. No.	Description		Cable Capacity (MCM)				Replacement
Cat. No.		Cu	AI	ACSR	EHS	Bolts	Blades
BAT20-7T13	Cable Cutter, No Heads (Includes bag, two 2 Ah batteries & charger)	-	-	-	_	-	-
BAT20-7T14	Cable Cutting/Crimper Kit (Includes 3 cutting heads, 3 crimping heads, bag, two 2 Ah batteries & charger)	750	1000	556	7/16"	3/8" Grade 8	BAT20-7T16 BAT20-7T17 BAT20-7T18
BAT20-7T3	Cable Cutter (includes Cu/Al Head)	750	1000	-	-	-	BAT20-7T16
BAT20-7T4	Cable Cutter (includes Cu/AI/ACSR Head)	500	500	556	-	-	BAT20-7T17
BAT20-7T5	Bolt Cutter (includes Steel Cutting Head)	-	-	-	7/16"	3/8" Grade 8	BAT20-7T18
BAT20-7T1	Cable Crimper (includes BG Fixed Die & D3 Groove Head)	600	350	477	-	-	-
BAT20-7T23	Cable Crimper (includes O Fixed Die & D3 Groove Head)	600	350	477	-	—	-
BAT20-7T2	Cable Crimper (includes D3 Groove Head)	600	350	477	-	-	-
7-Ton Mix 8	Match - Build Your Own Combination						
BAT20-7T	Cable Cutter/Crimper (includes tool and bag)	-	-	-	-	-	-
BAT20-7T6	Crimping Jaw, BG Fixed Die & D3 Groove	600	350	477	-	-	-
BAT20-7T7	Crimping Jaw, D3 Groove	600	350	477	-		-
BAT20-7T12	Crimping Jaw, O Fixed Die & D3 Groove	600	350	477	-	-	-
BAT20-7T9	Cutting Jaw, Cu/Al	750	1000	-	-	-	-
BAT20-7T10	Cutting Jaw, Cu/AI & ACSR	500	500	556	-	-	-
BAT20-7T11	Cutting Jaw, Steel	-	-	-	7/16"	3/8" Grade 8	



POWERED BY

EV/

D

4



[†]4 hour (4Ah) battery models available

www.kleintools.com

© 2019 Klein Tools, Inc. Lincolnshire, IL 60069 82804 Rev. 07/19 C