

Product data sheet

Specifications



UPS Network Management Card 2 w/ Environmental Monitoring, Out of Band Access and Modbus

AP9635

Overview

Lead time Usually in Stock

Main

Provided equipment CD with software
Temperature sensor
User manual

Physical

Height 3.81 cm

Width 12.1 cm

Depth 10.8 cm

Net weight 0.14 kg

Mounting preference No preference

Mounting mode Not rack-mountable

Conformance

Standards EN 55022 class A
FCC part 15 class A
ICES-003

Product certifications AS/NZS 3548 (C-Tick) class A
GOST
VCCI class A

Environmental

Ambient air temperature for operation -5...45 °C

Operating altitude 0...10000 ft

Relative humidity 0...95 % non-condensing

Ambient air temperature for storage -15...65 °C

Storage altitude 0.00...15240.00 m

Storage Relative Humidity 0...95 %

Communications & Management

Authentication Radius

Packing Units

Package 1 Weight	0.91 kg
Package 1 Height	5.1 cm
Package 1 width	23.5 cm
Package 1 Length	15.9 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Lead free	Yes
Mercury free	Yes
RoHS exemption information	Yes
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------