

Product data sheet

Specifications



APC Dry Contact I/O Accessory

AP9810



Overview

Presentation	UPS management accessory that provides two dry contact input and one relay output interface to APC UPS management offers with UIO ports such as the UPS Network Management Card (AP9641, AP9643) or Dry Contact I/O SmartSlot Card (AP9613).
Lead time	Usually in Stock

Main

Provided equipment	Cat 5 Ethernet cable User manual
---------------------------	-------------------------------------

Physical

Colour	Black
Height	2.2 cm
Width	4.52 cm
Depth	4.46 cm
Net weight	0.05 kg
Mounting preference	No preference
Mounting mode	Not rack-mountable

Conformance

Standards	EN 61000-4-2 EN 61000-4-3 EN 61000-4-4 EN 61000-4-6
------------------	--

Environmental

Ambient air temperature for operation	0...40 °C
Operating altitude	0...3333 ft
Relative humidity	0...95 %
Ambient air temperature for storage	-15...65 °C
Storage altitude	0.00...4572.00 m
Storage Relative Humidity	0...95 %

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Package 1 Weight	0.14 kg
Package 1 Height	3.3 cm
Package 1 width	25.4 cm
Package 1 Length	12.7 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Lead free	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------