

Product data sheet

Specifications



APC NetShelter SX, Server Rack Enclosure, 24U, Shock Packaging, 1250 lbs, Black, 1200H x 600W x 1070D mm

AR3104SP1

Overview

Presentation NetShelter SX cabinet and packaging system designed to safely integrate, transport, unload and deploy up to 1250 lbs (566 kg) of IT equipment. The cabinet is paired with a shock absorbing pallet, unloading ramp, and impact resistant shell. The system has been engineered, tested and approved for secure shipment of fully converged systems such as being certified with Cisco® for pre-racking and shipping Cisco Unified Computing System (UCS).

Lead time Usually in Stock

Main

Number of rack unit 24U

Provided equipment
Baying hardware
Doors
Installation guide
Keyed-alike doors and side panels
Leveling feet
Mounting hardware
Pallet ramps
Pre-installed casters
Reusable packaging
Roof
Side panels

Physical

Colour Black

Height 120 cm

Width 60 cm

Depth 107 cm

Net weight 89.09 kg

Mounting preference No preference

Mounting mode Not rack-mountable

Maximum mounting depth 91.49 cm

Minimum mounting depth 19.1 cm

Rack width 19"

Marking
14 gauge EIA mounting rail
16 gauge front door
16 gauge post
18 gauge rear door
18 gauge roof
18 gauge side panels

Permanent permissible load
1020.58 kg dynamic
1360.78 kg static

Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

Packing Units

Package 1 Weight	106.82 kg
Package 1 Height	135 cm
Package 1 width	89.9 cm
Package 1 Length	121.9 cm
Number of Units in Package 3	1

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------
