

# Product data sheet

Specifications



## APC NetShelter SX, Server Rack Enclosure, 45U, Black, 2124H x 600W x 1070D mm, TAA Compliant

AR3105TAA

### Overview

**Lead time** Special Order - Call for Quoted Lead Times

### Main

**Number of rack unit** 45U

**Provided equipment** Baying hardware  
Key(s)  
Keyed-alike doors and side panels  
Leveling feet  
Mounting hardware  
Pre-installed casters  
Side panels

### Physical

**Colour** Black

**Height** 212.4 cm

**Width** 60 cm

**Depth** 107 cm

**Net weight** 137 kg

**Mounting preference** No preference

**Mounting mode** Not rack-mountable

**Maximum mounting depth** 91.49 cm

**Minimum mounting depth** 19.1 cm

**Rack width** 19"

**Marking** 14 gauge EIA mounting rail  
16 gauge front door  
16 gauge post  
18 gauge rear door  
18 gauge roof  
18 gauge side panels

**Permanent permissible load** 1020.58 kg dynamic  
1700.97 kg static

### Conformance

**Product certifications** TAA compliance

**Standards** UL 2416  
UL 60950-1  
EIA-310E

## Packing Units

Package 1 Weight	153.7 kg
Package 1 Height	224 cm
Package 1 width	74.6 cm
Package 1 Length	122 cm
Number of Units in Package 3	1

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Take-back	Take-back program available

## Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------