

# Product data sheet

Specifications



## APC NetShelter SX, Server Rack Enclosure, 45U, White, 2124H x 600W x 1070D mm

AR3105W

### Overview

Lead time Usually in Stock

### Main

Number of rack unit 45U

Provided equipment

- Baying hardware
- Key(s)
- Keyed-alike doors and side panels
- Leveling feet
- Mounting hardware
- Pre-installed casters
- Side panels
- User manual

### Physical

Colour White

Height 212.4 cm

Width 60 cm

Depth 107 cm

Net weight 137 kg

Mounting preference No preference

Mounting mode Not rack-mountable

Maximum mounting depth 91.49 cm

Minimum mounting depth 19.1 cm

Rack width 19"

Marking

- 14 gauge EIA mounting rail
- 16 gauge front door
- 16 gauge post
- 18 gauge rear door
- 18 gauge roof
- 18 gauge side panels

Permanent permissible load

- 1020.58 kg dynamic
- 1700.97 kg static

### Conformance

Standards

- UL 2416
- UL 60950-1
- EIA-310E

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Packing Units

Package 1 Weight	153.7 kg
Package 1 Height	224 cm
Package 1 width	74.6 cm
Package 1 Length	122 cm
Number of Units in Package 3	1

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Take-back	Take-back program available

## Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------