

Product data sheet

Specifications



APC NetShelter SX, Server Rack Enclosure, 48U, without Doors, Black, 2258H x 600W x 1070D mm

AR3107X610

Overview

Presentation	Tall enclosure with 48U spaces for additional equipment. Compact width to optimize data center space. For low to medium density server and networking applications.
Lead time	Usually in Stock

Main

Number of rack unit	48U
Provided equipment	Baying hardware Key(s) Leveling feet Mounting hardware Pre-installed casters Side panels

Physical

Colour	Black
Height	225.8 cm
Width	60 cm
Depth	107 cm
Net weight	116.64 kg
Mounting preference	No preference
Mounting mode	Not rack-mountable
Maximum mounting depth	91.49 cm
Minimum mounting depth	19.1 cm
Rack width	19"
Marking	14 gauge EIA mounting rail 0 gauge front door 16 gauge post 0 gauge rear door 18 gauge roof 18 gauge side panels
Permanent permissible load	1020.58 kg dynamic 1360.78 kg static

Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
------------------	-----------------------------------

Packing Units

Package 1 Weight	136.09 kg
Package 1 Height	238.5 cm
Package 1 width	89.9 cm
Package 1 Length	121.9 cm
Number of Units in Package 3	1

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------