

Product data sheet

Specifications



APC NetShelter SX, Server Rack Enclosure, 48U, without Sides and Doors, Black, 2258H x 600W x 1070D mm

AR3107X617

Overview

Lead time Usually in Stock

Main

Number of rack unit 48U

Provided equipment Baying hardware
Key(s)
Leveling feet
Mounting hardware
Pre-installed casters

Physical

Colour Black

Height 225.8 cm

Width 60 cm

Depth 107 cm

Net weight 84.09 kg

Mounting preference No preference

Mounting mode Not rack-mountable

Maximum mounting depth 91.49 cm

Minimum mounting depth 19.1 cm

Rack width 19"

Marking 14 gauge EIA mounting rail
0 gauge front door
16 gauge post
0 gauge rear door
18 gauge roof
0 gauge side panels

Permanent permissible load 1020.58 kg dynamic
1360.78 kg static

Conformance

Standards UL 2416
UL 60950-1
EIA-310E

Packing Units

Package 1 Weight 103.55 kg

Package 1 Height	238.5 cm
Package 1 width	89.9 cm
Package 1 Length	121.9 cm
Number of Units in Package 3	1

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------