

Product data sheet

Specifications



APC NetShelter SX, Server Rack Enclosure, 42U, without Rear Doors, Black, 1991H x 750W x 1070D mm

AR3150HACS

Overview

Lead time Usually in Stock

Main

Number of rack unit 42U

Provided equipment
Casters
Doors
Ground studs
Installation guide
Leveling feet
Mounting hardware
Roof
Side panels

Physical

Colour Black

Height 199.1 cm

Width 75 cm

Depth 107 cm

Net weight 142.27 kg

Mounting preference No preference

Mounting mode Not rack-mountable

Rack width 19"

Marking
14 gauge EIA mounting rail
16 gauge front door
14 gauge post
18 gauge rear door
18 gauge roof
18 gauge side panels

Permanent permissible load
1020.58 kg dynamic
1700.97 kg static

Conformance

Standards
UL 2416
UL 60950-1
EIA-310E

Packing Units

Package 1 Weight 154.55 kg

| | |
|-------------------------------------|----------|
| Package 1 Height | 221.6 cm |
| Package 1 width | 89.5 cm |
| Package 1 Length | 121.9 cm |
| Number of Units in Package 3 | 1 |

Contractual warranty

| | |
|-----------------|--------------------------|
| Warranty | 5 year repair or replace |
|-----------------|--------------------------|
