

Product data sheet

Specifications



APC NetShelter SX, Server Rack Enclosure, 42U, without Sides, Black, 2258H x 750W x 1070D mm

AR3150X609

Overview

Presentation	Wide enclosure with increased cable management options for high density server and networking applications. 42U height to easily roll through doorways.
Lead time	Usually in Stock

Main

Number of rack unit	42U
Provided equipment	Baying hardware Casters Door key Doors Leveling feet Rack mounting hardware Roof

Physical

Colour	Black
Height	199.14 cm
Width	75 cm
Depth	107 cm
Net weight	126.86 kg
Mounting location	Front
Mounting preference	No preference
Mounting mode	Not rack-mountable
Maximum mounting depth	91.49 cm
Minimum mounting depth	26.19 cm
Rack width	19"
Marking	14 gauge EIA mounting rail 16 gauge front door 16 gauge post 16 gauge rear door 18 gauge roof
Permanent permissible load	1020.58 kg dynamic 1360.78 kg static

Conformance

Standards	UL 2416 UL 60950-1
------------------	-----------------------

Packing Units

Package 1 Weight	139.09 kg
Package 1 Height	221.6 cm
Package 1 width	89.5 cm
Package 1 Length	121.9 cm
Number of Units in Package 3	1

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------