

Product data sheet

Specifications



APC NetShelter SX, Server Rack Enclosure, 45U, White, 2124H x 750W x 1070D mm

AR3155W

Overview

Lead time Usually in Stock

Main

Number of rack unit 45U

Provided equipment

- Baying hardware
- Key(s)
- Keyed-alike doors and side panels
- Leveling feet
- Mounting hardware
- Pre-installed casters
- Side panels
- User manual

Physical

Colour White

Height 212.4 cm

Width 75 cm

Depth 107 cm

Net weight 155 kg

Mounting preference No preference

Mounting mode Not rack-mountable

Maximum mounting depth 91.49 cm

Minimum mounting depth 26.19 cm

Rack width 19"

Marking

- 14 gauge EIA mounting rail
- 16 gauge front door
- 16 gauge post
- 18 gauge rear door
- 18 gauge roof
- 18 gauge side panels

Permanent permissible load

- 1020.58 kg dynamic
- 1700.97 kg static

Conformance

Standards

- UL 2416
- UL 60950-1
- EIA-310E

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Package 1 Weight	172.3 kg
Package 1 Height	224 cm
Package 1 width	85 cm
Package 1 Length	132 cm
Number of Units in Package 3	1

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------