

# Product data sheet

Specifications



## APC NetShelter SX, Server Rack Enclosure, 48U, without Sides and Doors, Black, 1991H x 600W x 1200D MM

AR3157X617

### Overview

<b>Presentation</b>	Tall and wide enclosure with 48U spaces for additional equipment and increased cable management options for high density server and networking applications.
<b>Lead time</b>	Usually in Stock

### Main

<b>Number of rack unit</b>	48U
<b>Provided equipment</b>	Baying hardware Key(s) Leveling feet Mounting hardware Pre-installed casters

### Physical

<b>Colour</b>	Black
<b>Height</b>	225.8 cm
<b>Width</b>	75 cm
<b>Depth</b>	107 cm
<b>Net weight</b>	107.18 kg
<b>Mounting preference</b>	No preference
<b>Mounting mode</b>	Not rack-mountable
<b>Maximum mounting depth</b>	91.49 cm
<b>Minimum mounting depth</b>	26.19 cm
<b>Rack width</b>	19"
<b>Marking</b>	14 gauge EIA mounting rail 16 gauge post 18 gauge roof
<b>Permanent permissible load</b>	1020.58 kg dynamic 1360.78 kg static

### Conformance

<b>Standards</b>	UL 2416 UL 60950-1 EIA-310E
------------------	-----------------------------------

### Packing Units

<b>Package 1 Weight</b>	122.18 kg
-------------------------	-----------

Package 1 Height	240 cm
Package 1 width	89.5 cm
Package 1 Length	121.9 cm
Number of Units in Package 3	1

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Take-back	Take-back program available

## Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------