

Product data sheet

Specifications



APC NetShelter SX, Server Rack Enclosure, 42U, White, 1991H x 600W x 1200D mm

AR3300W

Overview

Lead time Usually in Stock

Main

Number of rack unit 42U

Provided equipment
Baying hardware
Key(s)
Keyed-alike doors and side panels
Leveling feet
Mounting hardware
Pre-installed casters
Side panels

Physical

Colour White

Height 199.1 cm

Width 60 cm

Depth 120 cm

Net weight 134.09 kg

Mounting preference No preference

Mounting mode Not rack-mountable

Maximum mounting depth 104.8 cm

Minimum mounting depth 19.1 cm

Rack width 19"

Marking
14 gauge EIA mounting rail
16 gauge front door
16 gauge post
18 gauge rear door
18 gauge roof
18 gauge side panels

Permanent permissible load
1020.58 kg dynamic
1700.97 kg static

Conformance

Standards
UL 2416
UL 60950-1
EIA-310E

Packing Units

| | |
|------------------------------|-----------|
| Package 1 Weight | 149.09 kg |
| Package 1 Height | 211.8 cm |
| Package 1 width | 75.2 cm |
| Package 1 Length | 133.4 cm |
| Number of Units in Package 3 | 1 |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| Take-back | Take-back program available |

Contractual warranty

| | |
|----------|--------------------------|
| Warranty | 5 year repair or replace |
|----------|--------------------------|