

Product data sheet

Specifications



APC NetShelter SX, Server Rack Enclosure, 42U, without Sides, Black, 1991H x 600W x 1200D mm

AR3300X609

Overview

Presentation	Deep Universal IT Enclosure for low to medium density server and networking applications that either require additional equipment clearance space or more open space for ease of access in the rear of the enclosure. Compact width to optimize data center space. 42U height to easily roll through doorways.
Lead time	Usually in Stock

Main

Number of rack unit	42U
Provided equipment	Baying hardware Key(s) Leveling feet Mounting hardware Pre-installed casters

Physical

Colour	Black
Height	199.1 cm
Width	60 cm
Depth	120 cm
Net weight	102.27 kg
Mounting preference	No preference
Mounting mode	Not rack-mountable
Maximum mounting depth	104.8 cm
Minimum mounting depth	19.1 cm
Rack width	19"
Marking	14 gauge EIA mounting rail 16 gauge front door 16 gauge post 18 gauge rear door 18 gauge roof
Permanent permissible load	1020.58 kg dynamic 1360.78 kg static

Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
------------------	-----------------------------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Package 1 Weight	117.27 kg
Package 1 Height	211.8 cm
Package 1 width	74.6 cm
Package 1 Length	133.4 cm
Number of Units in Package 3	1

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
Take-back	Take-back program available

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------