

Product data sheet

Specifications

APC SERVICE BYPASS PDU, 120V 15AMP W/ (8) NEMA 5-15R



SBP1500RM

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	120 V
Main Output Voltage	120 V
Plug standard	NEMA 5-15P
Number of rack unit	2U
Cable length	2.44 m
Number of cables	1
Provided equipment	User manual Rack mounting brackets

Physical

Colour	Black
Height	8.9 cm
Width	43.2 cm
Depth	7.6 cm
Net weight	2.95 kg
Mounting location	Front
Mounting preference	No preference
Mounting mode	Rack-mounted

Input

Network frequency	50/60 Hz
Permissible voltage	100...125 V
Max line current	15 A
Input current limits	15 A
Load capacity	1500 VA
Power factor	0...1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Output

Max current draw	15 A
Number of power socket outlets	8 NEMA 5-15R
Number of power socket outlets	8
Protection type	Circuit breaker
Power cable length	1.22 m
Efficiency	99 %

Conformance

Product certifications	TÜV
------------------------	-----

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Operating altitude	0...15000 ft
Ambient air temperature for storage	-15...45 °C
Storage Relative Humidity	0...95 %
Storage altitude	0.00...15240.00 m

Packing Units

Package 1 Weight	3.8 kg
Package 1 Height	15.1 cm
Package 1 width	46.3 cm
Package 1 Length	29.5 cm
Number of Units in Package 3	56

Offer Sustainability

EU RoHS Directive	Under investigation
-------------------	---------------------

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------