

# SMT1500RM2UC

APC Smart-UPS, Line Interactive, 1500VA,  
Rackmount 2U, 120V, 6x NEMA 5-15R outlets,  
SmartConnect Port+SmartSlot, AVR, LCD



## Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable run-time. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Lead time	Usually Ships within 2 Weeks

## Main

Input voltage	120 V
Input voltage	110 V 125 V
Output voltage	120 V
Output voltage	110 V 125 V
Rated power in W	1000 W
Rated power in VA	1440 VA
Plug standard	NEMA 5-15P
Nb of power socket outlets	6 NEMA 5-15R
Number of rack unit	2U
Cable length	2.44 M
Number of cables	1
Battery type	Lead-acid battery
Provided equipment	Installation guide Rack mounting support rails USB cable

## General

Number of power module filled slots	0
Number of power module free slots	0
Additional specification	Cloud-enabled monitoring
Redundant	No

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Physical

Colour	Black
Height	8.6 Cm
Width	43.2 Cm
Depth	47.7 Cm
Net weight	26.5 Kg
Mounting location	Front
Mounting preference	Lower
Mounting mode	Rack-mounted
Two post mountable	0
USB compatible	Yes

## Input

Input voltage limits	75...154 V adjustable 82...144 V
Network frequency	50/60 Hz +/- 3 Hz auto-sensing

## Output

Harmonic distortion	Less than 5 %
Maximum configurable power in VA	1440 VA
Maximum configurable power in W	1000 W
Transfer time	6 ms typical : 10 ms maximum
UPS type	Line interactive
Wave type	Sine wave
Output frequency	50/60 Hz +/- 3 Hz sync to mains

## Conformance

Product certifications	CULus ENERGY STAR V2.0 (USA)
Equipment protection policy	Lifetime : \$150000
Standards	CSA C22.2 No 107.1 FCC part 15 class A ICES-003 UL 1778

## Environmental

Acoustic level	45 dBA
Heat dissipation	225 Btu/H
Operating altitude	0...10000 ft
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...15240.00 M
Relative humidity	0...95 %
Storage Relative Humidity	0...95 %

## Batteries & Runtime

Extended runtime	0
Battery design life	3...5 Year(S)
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	3 H
Number of battery replacement quantity	1
Battery life	3...5 Year(S)
Battery power in VAH	432 VAh runtime
Battery charger power	144 W rated

## Communications & Management

Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Control panel	Multifunction LCD status and control console
Free slots	1

## Surge Protection and Filtering

Surge energy rate	680 J
Noise suppression	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

## Packing Units

Package 1 Weight	32.12 Kg
Package 1 Height	23.5 Cm
Package 1 width	59 Cm
Package 1 Length	61 Cm
Number of Units in Package 3	8

## Offer Sustainability

Sustainable offer status	Green Premium product
ENERGY STAR®	<a href="#">ENERGY STAR UPS V2.0 (USA)</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

## Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
----------	---

Product Life Status : **Commercialised**