

SMTL750RM2UC

APC Smart-UPS, Line Interactive, 750VA,
Lithium-ion, Rack/Tower, 2U, 120V, 6x NEMA
5-15R outlets, SmartConnect Port+SmartSlot,
Short Depth, AVR, LCD



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Input voltage	120 V
Output voltage	120 V
Rated power in W	600 W
Rated power in VA	750 VA
Plug standard	NEMA 5-15P
Nb of power socket outlets	6 NEMA 5-15R
Number of rack unit	2U
Cable length	2.44 M
Number of cables	1
Battery type	Li-Ion (Lithium-Ion)
Provided equipment	CD with software Documentation CD Installation guide Rack mounting support rails Smart UPS signalling RS-232 cable USB cable

Physical

Colour	Black
Height	8.6 Cm
Width	43.8 Cm
Depth	31.8 Cm
Net weight	15.42 Kg
Mounting location	Front
Mounting preference	Lower
Mounting mode	Rack-mounted
Two post mountable	1
USB compatible	Yes

Input

Network frequency	50/60 Hz +/- 3 Hz auto-sensing
Input voltage limits	75...154 V adjustable 82...144 V

Output

Maximum configurable power in W	600 W
Harmonic distortion	Less than 5 %
Output frequency	50/60 Hz +/- 3 Hz sync to mains
UPS type	Line interactive
Wave type	Sine wave

Conformance

Product certifications	NOM
Standards	CSA C22.2 No 107.3 FCC part 15 class A UL 1778 UL 1973
Equipment protection policy	Lifetime : \$150000

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...10000 ft
Ambient air temperature for storage	-40...35 °C
Storage Relative Humidity	0...95 % Non-condensing
Storage altitude	0.00...7620.00 M
Acoustic level	41 dBA
Heat dissipation	70 Btu/H

Batteries & Runtime

Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	3 H

Communications & Management

Free slots	1
Control panel	Multifunction LCD status and control console
Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays

Surge Protection and Filtering

Surge energy rate	680 J
Noise suppression	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

Packing Units

Package 1 Weight	17.69 Kg
Package 1 Height	22.9 Cm
Package 1 width	58.4 Cm
Package 1 Length	47.2 Cm
Number of Units in Package 3	16

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Optimized Energy Efficiency	Energy efficient product

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------

Product Life Status : **Commercialised**