

NEMA Full Voltage Power Devices

NEMA Rated Full Voltage Contactors

CR305, CR385 Magnetic Contactors

Three-phase, Three-Pole

Nonreversing, Open, NEMA Type 1, 3R, 12, 4/4X

NEMA Sizes 00-9

600 Volts Maximum 50/60 Hertz

Three-Pole:

CR305, Three-Phase, 3-Pole Magnetic Contactors NEMA sizes 00-6

NEMA Size	Continuous Ampere Rating ¹		Voltage @ 60 Hz	Horsepower	Open Type		NEMA Type 1		NEMA Type 3R		NEMA Type 12		NEMA Type 4/4X	
	Enclosed	Open			Product Number CR305	Product Number CR305	Product Number CR305	List Price GO-10G	Product Number CR305	List Price GO-10G	Product Number CR305	List Price GO-10G	Product Number CR305	List Price GO-10G
00	9A	10A	115-120	—	A002	A102	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	
00	9A	10A	200-208	1 1/2	A023	A123	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	
00	9A	10A	230-240	1 1/2	A003	A103	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	
00	9A	10A	460-480	2	A004	A104	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	
00	9A	10A	575-600	2	A005	A105	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	Use NEMA Size 0	
0	18A	20A	115-120	—	B002	B102	B602	B202	B402					
0	18A	20A	200-208	3	B023	B123	B623	B223	B423					
0	18A	20A	230-240	3	B003	B103	B603	B203	B403					
0	18A	20A	460-480	5	B004	B104	B604	B204	B404					
0	18A	20A	575-600	5	B005	B105	B605	B205	B405					
1	27A	30A	115-120	—	C002	C102	C602	C202	C402					
1	27A	30A	200-208	7 1/2	C023	C123	C623	C223	C423					
1	27A	30A	230-240	7 1/2	C003	C103	C603	C203	C403					
1	27A	30A	460-480	10	C004	C104	C604	C204	C404					
1	27A	30A	575-600	10	C005	C105	C605	C205	C405					
2	45A	50A	115-120	—	D002	D102	D602	D202	D402					
2	45A	50A	200-208	10	D023	D123	D623	D223	D423					
2	45A	50A	230-240	15	D003	D103	D603	D203	D403					
2	45A	50A	460-480	25	D004	D104	D604	D204	D404					
2	45A	50A	575-600	25	D005	D105	D605	D205	D405					
3	90A	100A	115-120	—	E002	E102	E602	E202	E402					
3	90A	100A	200-208	25	E023	E123	E623	E223	E423					
3	90A	100A	230-240	30	E003	E103	E603	E203	E403					
3	90A	100A	460-480	50	E004	E104	E604	E204	E404					
3	90A	100A	575-600	50	E005	E105	E605	E205	E405					
4	135A	150A	115-120	—	F002	F102	F602	F202	F402					
4	135A	150A	200-208	40	F023	F123	F623	F223	F423					
4	135A	150A	230-240	50	F003	F103	F603	F203	F403					
4	135A	150A	460-480	100	F004	F104	F604	F204	F404					
4	135A	150A	575-600	100	F005	F105	F605	F205	F405					
5	270A	300A	115-120	—	G002	G102	G602	G202	G402					
5	270A	300A	200-208	75	G023	G123	G623	G223	G423					
5	270A	300A	230-240	100	G003	G103	G603	G203	G403					
5	270A	300A	460-480	200	G004	G104	G604	G204	G404					
5	270A	300A	575-600	200	G005	G105	G605	G205	G405					
6	540A	600A	115-120	—	HH002	HH102AA2A	HH602AA2A	HH202AA2A	HH402AA2A					
6	540A	600A	200-208	150	HH023	HH123AA2A	HH623AA2A	HH223AA2A	HH423AA2A					
6	540A	600A	230-240	200	HH003	HH103AA2A	HH603AA2A	HH203AA2A	HH403AA2A					
6	540A	600A	460-480	400	HH004	HH104AA2A	HH604AA2A	HH204AA2A	HH404AA2A					
6	540A	600A	575-600	400	HH005	HH105AA2A	HH605AA2A	HH205AA2A	HH405AA2A					

CR385, Three-Phase, 3-Pole Magnetic Contactors NEMA sizes 7-9

¹Motor full-load current should not exceed continuous ampere rating of contactor.

NEMA Size	Continuous Ampere Rating ¹	Control Motor Voltage	Horsepower	Circuit Voltage	Open Type
					Product Number CR385
7	900A	N/A	—	115	J002AA1A
7	900A	220-240	300	230	J003AA1A
7	900A	440-480	600	460	J004AA1A
7	900A	550-600	600	575	J005AA1A
8	1350A	N/A	—	115	K002AA1A
8	1350A	220-240	450	230	K003AA1A
8	1350A	440-480	900	460	K004AA1A
8	1350A	550-600	900	575	K005AA1A
9	2500A	N/A	—	115	L002AA1A
9	2500A	220-240	800	230	L003AA1A
9	2500A	440-480	1600	460	L004AA1A
9	2500A	550-600	1600	575	L005AA1A

