

CR360L

Electrically held contactors

CR360L - 30A - 300A (2, 3 & 4 pole) (continued)

CR360L



1: Select size, number of poles, and enclosure

Open

Continuous amp rating	No. of poles	Product number
30A	2	CR360L302
30A	3	CR360L303
30A	4	CR360L304
60A	2	CR360L402
60A	3	CR360L403
60A	4	CR360L404
100A	2	CR360L502
100A	3	CR360L503
100A	4	CR360L504
200A	2	CR360L602
200A	3	CR360L603
200A	4	CR360L604
300A	2	CR360L702
300A	3	CR360L703
300A	4	CR360L704

Enclosed NEMA Type 1

Continuous amp rating	No. of poles	Product number
30A	2	CR360L312
30A	3	CR360L313
30A	4	CR360L314
60A	2	CR360L412
60A	3	CR360L413
60A	4	CR360L414
100A	2	CR360L512
100A	3	CR360L513
100A	4	CR360L514
200A	2	CR360L612
200A	3	CR360L613
200A	4	CR360L614
300A	2	CR360L712
300A	3	CR360L713
300A	4	CR360L714

Enclosed NEMA Type 12

Continuous amp rating	No. of poles	Product number
30A	2	CR360L322
30A	3	CR360L323
30A	4	CR360L324
60A	2	CR360L422
60A	3	CR360L423
60A	4	CR360L424
100A	2	CR360L522
100A	3	CR360L523
100A	4	CR360L524
200A	2	CR360L622
200A	3	CR360L623
200A	4	CR360L624
300A	2	CR360L722
300A	3	CR360L723
300A	4	CR360L724

Enclosed NEMA Type 3R

Continuous amp rating	No. of poles	Product number
30A	2	CR360L362
30A	3	CR360L363
30A	4	CR360L364
60A	2	CR360L462
60A	3	CR360L463
60A	4	CR360L464
100A	2	CR360L562
100A	3	CR360L563
100A	4	CR360L564
200A	2	CR360L662
200A	3	CR360L663
200A	4	CR360L664
300A	2	CR360L762
300A	3	CR360L763
300A	4	CR360L764

Enclosed NEMA Type 4, SS

Continuous amp rating	No. of poles	Product number
30A	2	CR360L322
30A	3	CR360L323
30A	4	CR360L324
60A	2	CR360L422
60A	3	CR360L423
60A	4	CR360L424
100A	2	CR360L522
100A	3	CR360L523
100A	4	CR360L524
200A	2	CR360L622
200A	3	CR360L623
200A	4	CR360L624
300A	2	CR360L722
300A	3	CR360L723
300A	4	CR360L724

