

# LUNA 🔕

# 4" Regressed Gimbal, Tunable White, Wi-Fi, 850 Lumens, 12W

Recessed Downlighting

Job Information		
Project Name		Туре
Location		
Quantity		Date
Contact/Phone		
Notes		

# **Features**

### **Body**

Durable airtight aluminum body with adjustable regressed gimbal. Includes anodized blue heat sink to provide maximum airflow for the LED light source.

# **LED Characteristics**

This general application light fixture features a 12 watt LED module that maintains uniform intensity producing up to 850 lumens; with a typical CRI of 90. Tunable White 2700 K to 5000 K color temperatures.

### Dimming

100%-2% Wi-Fi dimming capability. Dimming controlled via the WiZ App and Room Controller.

## **Beam Spread**

The fixture lens provides 38° beam spread.

# Mounting

Includes two spring loaded clips to attached to any ceiling material.

## **LED Driver**

Extruded aluminum hardwire box with

12 watt (300mA) Wi-Fi dimmable LED driver with 100-135V AC input. Includes an 18" wire with 3-Pin DC connector between driver and fixture.

# WiZ App

Can be controlled via the WiZ App (works with iOS and Android) from anywhere. Voice control can also be achieved by integrating the app with most smart speakers. Works with Google Assistant, Siri, Alexa and IFTTT.

# Quick Connect push-in terminals

Three "Quick connect" push-in terminals for fast and easy wiring.

# **Minimum Starting Temperature** -40°C (-40°F)

# **Environment**

- Suitable for wet locations.
- Approved for direct contact with insulation.
- Suitable for indoor/outdoor applications
- Airtight

# QuickShip In-Stock

In-Stock products ship within two business days of an order being released.\*

SPECIFICATION				
Application	Ceiling Recess Mount			
Approved Location	Wet / Insulated Ceilings /			
	Indoor / Outdoor			
Beam Angle	38°			
CCT	Tunable White			
	(2700 K - 5000 K)			
Certification	cETLus			
Class II	Yes			
Colour	BK / BN / WH			
CRI	90			
Dimming	Yes			
Dimming Tech	Wi-Fi Dimming (via WiZ			
Diffilling recit	App)			
Energy Star	Yes			
Hole Cut	Ø 41/4" (108mm)			
Input	100-135V AC, 60Hz			
Lumens	Up to 850			
Lumens per Watt	Up to 71			
Power Factor	0.9			
Projected Life	70% @ 50,000 hrs			
Warranty	3-Year			
Wattage	12W			



# Description


works with the Google Assistant

Siri Shortcuts


representative.

change without notice.

Evolved to be a flexible, low-glare, and aesthetically pleasing luminaire, the LUNA OnCloud offers contractors, builders, homeowners and designers, a fixture with regressed optics, Tunable White and Wi-Fi dimming abilities, to promote on-site flexibility, while enhancing sleek, directional lighting in both commercial and residential spaces.



# **Ordering Guide**



<sup>\*</sup> QuickShip lead time may vary for orders greater than 100 pieces. No additional shipment rates apply. Subject to availability.



alexa

**AIR** 

**TIGHT** 

IFTTT

RATED

WET LOCATION ENDROITS MOUILLÉS

**Notes:** Accessories are sold separately. For additional options please consult your Liteline

Due to our continued efforts to improve our products, product specifications are subject to

# Accessories



# P-4020

4¼" Round pre-mounting plate with driver attachment clip, for 4" LUNA LED



# P-4020NC

41/4" Round new construction plate with driver attachment clip, for 4" LUNA LED fixtures.



# P-NCMK-1

New construction mounting kit. Includes hanger bars, brackets and screws.



RA4-XLRING-BK
Reducer ring for 4" LUNA fixtures, black.



# **RA4-XLRING-BN**

Reducer ring for 4" LUNA fixtures, brushed nickel.



# **RA4-XLRING-WH**

Reducer ring for 4" LUNA fixtures, white.



Vapour barrier extender. For use in new construction applications.



# LC-CRTL-SCENE-1

OnCloud Room Controller, Wi-Fi, ON/ OFF, CCT, Dimming and favourite



Vapour barrier extender. For use in remodel applications.



# VBE-5

Vapour barrier extender. For use in new construction applications.