



LED PAR30 S/L

10PAR30L/LED/827/F40/DIM/ULW/120V 6/1FB

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

Product data

General information	
Cap-Base	E26 [Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	25000 h
Switching Cycle	25000X
Technical Type	10-75W
Light technical	
Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	40 °
Luminous Flux (Nom)	800 lm
Luminous Intensity (Nom)	1600 cd
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	80.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom) 70 %	
Operating and electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	10 W
Lamp Current (Nom)	86 mA
Wattage Equivalent	75 W


Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	67 °C
Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Bulb Shape	PAR30L [PAR 3.75 inch/95mm Long]
Approval and application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh
Product data	
Order product name	10PAR30L/LED/827/F40/DIM/ULW/120V
	6/1FB
EAN/UPC - Product	046677529734
Order code	529735
Numerator - Quantity Per Pack	1

Datasheet, 2021, February 28 data subject to change

LED PAR30 S/L

Numerator - Packs per outer box	6
Material Nr. (12NC)	929001322004
Net Weight (Piece)	0.285 kg


Dimensional drawing




10PAR30L/LED/827/F40/DIM/ULW/120V 6/1FB

Product D C 10PAR30L/LED/827/F40/DIM/ULW/120V 6/1FB 94 mm 118 mm


Photometric data



10-75W E26 PAR30L 40D 827 2700K




10-75W E26 PAR30L 40D 827 2700K




10-75W E26 PAR30L

LED PAR30 S/L

Lifetime





14-120W E26 PAR38

14-120W E26 PAR38



© 2021 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.