



# LED PAR38

## 14PAR38/LED/840/F40/DIM/ULW/120V 6/1FB

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

### Product data

General information	
Cap-Base	E26 [ Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	25000 h
Switching Cycle	25000X
Technical Type	14-120W
Light technical	
Color Code	841 [ CCT of 4100K (841)]
Beam Angle (Nom)	40 °
Luminous Flux (Nom)	1200 lm
Luminous Intensity (Nom)	2500 cd
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	85.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	14 W
Lamp Current (Nom)	120 mA
Wattage Equivalent	120 W

Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	70 °C
Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Bulb Shape	PAR38 [ PAR 4.75 inch/121mm]
Approval and application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	- kWh
Product data	
Order product name	14PAR38/LED/840/F40/DIM/ULW/120V 6/1FB
EAN/UPC - Product	046677529604
Order code	529602
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6

# LED PAR38


Material Nr. (12NC)	929001319104
Net Weight (Piece)	0.385 kg

## Dimensional drawing

Product	D	C
14PAR38/LED/840/F40/DIM/ULW/120V 6/1FB	122 mm	134 mm

14PAR38/LED/840/F40/DIM/ULW/120V 6/1FB


## Photometric data



Access Lighting - Spot

14-120W E26 PAR38 40D 840 4000K


14-120W E26 PAR38 40D 840 4000K



14-120W E26 PAR38

# LED PAR38

## Lifetime



14-120W E26 PAR38

14-120W E26 PAR38

