



# LED Highbay

## 65HB/LED/850/ND FB 4/1

Philips LED high bay lamps are a direct replacement for 250W to 400W metal halide lamps which will deliver substantial energy savings. Available in both plug-and-play (UL Type A) and MainsFit (UL Type B) options, Philips LED HighBays delivers bright, clean light for a fraction of the energy used by conventional HID.

### Product data

General information	
Cap-Base	EX39 [ Exclusionary Mogul Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Technical Type	65-150W
Light technical	
Color Code	850 [ CCT of 5000K]
Beam Angle (Nom)	240 °
Luminous Flux (Nom)	7000 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	107.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	65 W
Lamp Current (Nom)	545 mA
Wattage Equivalent	150 W


Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
UL Type	Type B - bypass the ballast
Power Factor (Nom)	0.9
Voltage (Nom)	120-277 V
Temperature	
T-Case Maximum (Nom)	98 °C
Controls and dimming	
Dimmable	No
Mechanical and housing	
Bulb Finish	Frosted
Bulb Shape	T-shape
Approval and application	
Energy Consumption kWh/1000 h	- kWh
Product data	
Order product name	65HB/LED/850/ND FB 4/1
EAN/UPC - Product	046677542290
Order code	929001990304

# LED Highbay

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	929001990304

Net Weight (Piece)	0.648 kg
--------------------	----------


## Dimensional drawing




65HB/LED/850/ND FB 4/1

Product	D	C
65HB/LED/850/ND FB 4/1	141 mm	267 mm


## Photometric data



LEDTrueForce HB EX39 200D 65





LEDTrueForce HB EX39 200D 65 850



LEDTrueForce HB EX39 200D 65 850

# LED Highbay

## Lifetime



LEDTrueForce HB EX39 200D

LEDTrueForce HB EX39 200D

