



Luminaire Wraparound

Project:
Location:
Cat.No:
Type:
Notes:



The Pila WP LED wraparound is a versatile surface mount luminaire. It is a sleek, low profile, low glare option for general illumination of hallways, storage areas, retail, and other commercial areas.

Product offering

Catalog Code	Description	UPC Code	Case Qty. (pc/carton)	Pallet Qty. (pc/pallet)
WP440L40KU	4' Wraparound, 48W, 4000 LUMENS, 4000K, 120-277V	190096130924	8	72

Technical specifications

Nominal power	46W
Nominal lumens	4000lm
Input voltage	120-277V, 50/60Hz
CCT	4000K
CRI	>80
Material and finishing	White polycarbonate housing, frosted polycarbonate lens
Mounting	Ceiling mounted, bag parts included: wirenuts (3), wood screws (4), drywall anchor bolts (4)
Linking	Power links included: flush connector, 5' cable connector
Weight	3.3lb (1.5kg)
IP/IK rating	IP20 / IK03

Operating temperature range	14F to 95F (-10C to 35C)
Lifetime	30K hrs @ L70 B50 @ Ta 25°C
Compliance	cETLus listed for use in damp locations
Warranty	3-year limited warranty





Dimensions

