
THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



DADT NO	BUNDLE MIN. (mm)	in	A in (mm)	B in (mm)	C in (mm)	in (mm)	in (mm)	F in (mm)	MIN. LOOP TENSILE 16s.	CROSS SECTION	APPROXIMATE WEIGHT   lbs/100 PARTS (g)
UCT3S	.63 (16.0)	3.0 (76.2)	.100	.85 (21.6)	.45 (11.4)	.14	1.10	12.0 (305)	50 (222)	STANDARD	.59 (267)
UCT5S	.63 (16.0)	5.0 (127)	.100 (2.5)	.85 (21.6)	.45 (11.4)	.14 (3.6)	1.10	18.0 (457)	50 (222)	STANDARD	.81 (366)

## NOTES:

1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND COLOR. 2) MINIMUM 2" OVERLAP REQUIRED TO ACHIEVE LOOP TENSILE RATING.

										DIMENSIONS IN PARENTHESIS ARE IN METRIC UNITS.			
												SS_27366_0	00.PRT
										CORP. TINLEY PARK, ILLINOIS			
										TAK-TY HOOK & LOOP CABLE TIES ULTRA-CINCH HOOK & LOOP TIES			
											HERWISE SPECIFIED, NAL TOLERANCES ARE:	UNLESS OTHERWISE SPECIFIED,	
										(.X) ± .	25 (.XXX) ± .030 125 ANGLES ±	ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
8	1/13/12	CR-MBA	DJW	ALTERNATE MATERIAL ADDED; SPECIFIC COLOR REMOVED:	SS-27366	8	KLN			DRAWN BY  JABO	MAT'L:	scale NONE	
7	4/12/06	FAB	DWW	ADDED PART WEIGHTS	27366	7	TGS			6/19/02	WOVEN HOOK/LOOP NYLON OR POLYESTER	DRAWING NO.	DWG
REV	DATE	BY	СНК	DESCRIPTION	ECN -	R	CUST	SUP		□WW chk.p		SS-27366	SIZE