

Opticom Rack Mount Fiber Enclosures


Part Numbers: FRME3, FRME4

INSTALLATION INSTRUCTIONS FS097 © Panduit Corp. 2014

FRME3 1 FRME Enclosure 1 FRME Kit 1 Port I.D. Label 2 Enclosure Brackets

FRME4

- 1 FRME Enclosure
- 1 FRME Kit



Assembly Instructions:

Determine the cable entry location on the enclosure. Remove the knockout by inserting a screwdriver into the slot located in the center of the knockout and apply a twisting upward motion, then lift out. Insert grommet following proper cutting diagram. Snap in saddle clips. Grounding lug attaches to a stud at the rear, inside the enclosure, on the top or bottom with a #10-32 nut. Apply laser warning label and caution label in a clearly visible location. Apply port I.D. label(s) on the inside of the door.

GROMMET CUTTING DIAGRAM








Cut the large circle for 1-1/2" diameter innerduct




Cut the straight lines when not using any innerduct






Attach strain relief clip with the #10-32 screw and nut provided.

Mounting Instructions




Bracket orientation for 23 inch rack

Attach the short leg of the bracket to the enclosure.



Bracket orientation for flush mount on a 19 inch rack


Locate rack bracket on the front mounting holes for flush mounting



Bracket orientation for projection mount on a 19 inch rack

Locate rack bracket on the mid enclosure mounting holes for projection mounting

Label Installation



For Instructions in Local Languages and Technical Support:

www.panduit.com/resources/install_maintain.asp

PANDUIT www.panduit.com

E-mail: techsupport@panduit.com Phone: 866-405-6654