


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

TECHNICAL SPECIFICATIONS

MAXIMUM LOSS		SINGLEMODE MAXIMUM LOSS	
3.5dB/KM @ 850nm 1.5dB/KM @ 1300nm		.75dB/KM @ 1310nm .75dB/KM @ 1500nm	
TENSILE LOAD - OFCR		TENSILE LOAD - OFCR-LS/OFCP	
INSTALLATION	LONG TERM	INSTALLATION	LONG TERM
660 N (150 lbf)	165 N (37 lbf)	440 N (100 lbf)	110 N (24 lbf)
	OFCR	OFCR-LS/OFCP	
OPERATION	-20° C TO +50° C (-4° F TO +122° F)		0° C TO +50° C (+32° F TO +122° F)
INSTALLATION			
STORAGE	-40° C TO +65° C (-40° F TO +149° F)		




NOTES:

1. DIAMETER DIMENSION, SHOWN FOR REFERENCE ONLY.
2. DIMENSIONS IN BRACKETS () ARE ENGLISH.
3. ALL MATERIALS AND COMPONENTS USED MUST MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.

OPTI-CORE 6 FIBER INTERLOCKING ARMORED DISTRIBUTION CABLE
CUSTOMER DRAWING



PANDUIT™
CORP.
TINLEY PARK, ILL 60477



ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.
DIMENSIONAL TOLERANCES ARE:
(.X) (.XXX) ±0.3 (.010)
(.XX) ±0.8 (.03) ANGLES

DRAWING FILENAME
M02055BW_DC_06/01A

SCALE
NONE

DRAWN BY
MC

REVIEW DRAWING NUMBERS

PART NO. FSP**06Y
FOP**06Y

DATE
06-03-05

DRAWING NO.
02055-98

SIZE
A

CHK'D
WMA

SHEET 1 OF 2

02	10-26-09	EFK		RELEASED TO PRODUCTION	02055-98					
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	

