



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
NK6XPP24P	.85 LB/10 PCS (383.6 g/EACH PC)

NOTES:

- SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
- SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
- DIMENSIONS IN PARENTHESES ARE IN METRIC.
- THE PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
- USE 110 STYLE TERMINATION TOOL FOR PUNCHDOWN.
- PART INCLUDES:
 - 1-PATCH PANEL ASSEMBLY
 - 4-LABEL COVERS
 - 4-LABELS
 - 1-SCREW KIT (INCLUDES FOUR (4) #12-24 SCREWS)
 - 1-SCREW KIT (INCLUDES FOUR (4) M6 SCREWS)
 - 24-RETENTION CAPS
- RETENTION CAPS ARE PROVIDED FOR SNAP-IN ON TERMINATED CONNECTORS.
- LABELS ARE PRE-NUMBERED (1-24 WITH BLANK SIDE FOR CUSTOM LABELING.



PART NUMBER		SEE CHART	
TITLE			
NETKEY 24 PORT ALL MOLDED CATEGORY 6A PUNCHDOWN PATCH PANEL			
CUSTOMER DRAWING			
ITEM REVISION NAME		10M163AG/00	
DATASET FILE NAME		10M163AG_DC02/00A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		MATERIAL:	
.x ± .xxx ± .010 (.3)		BASE-REINFORCED PBT COVER-ABS	
.xx ± .03 (.8) ANGLES ±			
DRAWING NUMBER:		10M163AG-02	
DRAWN BY	DATE	CHK	SCALE
BJN	2-4-15	MDJR	NONE
REV	DATE	BY	CHK
R	2-4-15	BJN	MDJR
APR		LPH	
DESCRIPTION		ECN	
RELEASED TO PRODUCTION		10M163AG-02	
SHT 1 OF 1		A	

D10100DA/14